

Coaxial Cable Connector 16_MMCX-50-1-1/111_O

Description

Right angle cable plug

Interface standards
SUHNER-MMCX



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 6 GHz

Mechanical Data

Centre contact soldered
Outer 2contact crimped
Weight 0.0007 kg

Environmental Data

Operating temperature -55 °C to 155 °C
2011/65/EU (RoHS) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Bronze	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (without Nickel underplating)
Body	Brass	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	
Crimp ferrule	Brass	

Related Documents

Outline drawing DOU-00006008
Catalogue drawing DOU-00006007
Assembly instruction DOC-0000179222

Ordering Information

Single package 16_MMCX-50-1-1/111_OE
Bulk 100 pcs package 16_MMCX-50-1-1/111_OH

Additional Information

Suitable cables RG_178_B/U, RG_196_A/U