


Minimum cable diameter: 3  
 Maximum cable diameter:  
 - with rubber bushing: 8  
 - without rubber bushing: 8,5  
 - without reduction plate: 12,5

			Dot.	Name	 All Dim. in mm Orig. Size DIN A 4
			Detail.	15/11/04 TR	
			Insp.		
			Stand.		

D-Sub, 25 poles,  
 top entry,  
 straight metal hood

Maßstab/  
 Scale  
 1,5:1

09 67 025 0349	M3
09 67 025 0344	4-40 UNC
Part number	Screw thread

EC00368	07/07/09	PK
32329	15/11/04	TR
Mod.	Dot.	Name

HARTING EURL  
 F-95972 Paris



TB 09 67 025 034X

Sub.

Blatt/ Page  
 2 / 2