



HelaGuard Accessories

• ALSS Stainless Steel Locknuts



HelaGuard ALSS Stainless Steel Locknuts.

Technical Table

Article-No.	Type	Thread Size (metric)	Pack Cont.
166-50126	ALSS-M16	M16	10
166-50127	ALSS-M20	M20	10
166-50128	ALSS-M25	M25	10
166-50129	ALSS-M32	M32	2
166-50130	ALSS-M40	M40	1
166-50131	ALSS-M50	M50	1
166-50132	ALSS-M63	M63	1

All dimensions in mm. Subject to technical changes.

Material Data

Material	Stainless Steel (SS316)
Colour	Metal (ML)
Operating Temperature	-100 °C to +400 °C



• ALPA PA66 Locknuts



HelaGuard ALPA PA66 Locknuts.

Technical Table

Article-No.	Type	Thread Size (metric)	Thread Size (PG)	Pack Cont.
166-50133	ALPA-M12	M12	–	10
166-50134	ALPA-M16	M16	–	10
166-50135	ALPA-M20	M20	–	10
166-50136	ALPA-M25	M25	–	10
166-50137	ALPA-M32	M32	–	2
166-50138	ALPA-M40	M40	–	1
166-50139	ALPA-M50	M50	–	1
166-50140	ALPA-M63	M63	–	1
166-50141	ALPA-PG7	–	PG7	10
166-50142	ALPA-PG9	–	PG9	10
166-50143	ALPA-PG11	–	PG11	10
166-50144	ALPA-PG13	–	PG13.5	10
166-50145	ALPA-PG16	–	PG16	10
166-50146	ALPA-PG21	–	PG21	10
166-50147	ALPA-PG29	–	PG29	1
166-50148	ALPA-PG36	–	PG36	1
166-50149	ALPA-PG42	–	PG42	1
166-50150	ALPA-PG48	–	PG48	1

All dimensions in mm. Subject to technical changes.

Colour grey available on request.

Material Data

Material	Polyamide 6.6 (PA66)
Colour	Black (BK)
Operating Temperature	-50 °C to +135 °C

