


SRD-TYPE



Unit : mm

Item No.	W	W1	H	H1	Length
SRD-25	25.4±3	7.4	5.8	3.8	1830
SRD-50	50.8±3	14.8	11.6	7.8	
SRD-65	66±3	19	15.3	10.9	
SRD-75	76.2±3	22	17.4	11.6	
SRD-100	101.6±3	29.4	23.2	15.4	



		MATERIAL	ITEM NO.
		P.V.C.	SRD-TYPE
SCALE		FINISH	NAME
			SOFT WIRING DUCT
△	(. .)	TOLERANCE±0.5mm	△ 03-10-2009 DATE
			REVISIONS K001
			R.NO.

