

Valve connectors - SACC-V-4CON-PG7/C-3+PE - 1511967

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Valve connector, 4-pos., type C, unconnected, screw connection, cable screw connection Pg7

Key commercial data

package_quantity	1
GTIN	4017918909345

Technical data

Dimensions

External diameter	4 mm ... 6 mm
-------------------	---------------

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C (plug connectors)
Degree of protection	IP65

General

Rated current at 40°C	10 A
Rated voltage	240 V
Number of positions	4
Contact resistance	≤ 15 mΩ
Insulation resistance	≥ 100 MΩ
Status display	No
Protective circuit/component	Unwired
Surge voltage category	II
Pollution degree	3
Connection method	Screw connection
Conductor cross section	0.34 mm ² ... 1.5 mm ²
AWG conductor cross section	22 ... 16

Material

Inflammability class according to UL 94	HB
Valve plug contact material	CuSn
Valve plug contact surface material	Ni
Valve plug contact insert material	PA6
Material housing valve plug	PA6

Valve connectors - SACC-V-4CON-PG7/C-3+PE - 1511967

Technical data

Material

Sealing material	NBR
------------------	-----

classifications

eCl@ss

eCl@ss 4.0	27140815
eCl@ss 4.1	27140815
eCl@ss 5.0	27143423
eCl@ss 5.1	27143423
eCl@ss 6.0	27143423
eCl@ss 7.0	27449001
eCl@ss 8.0	27449001

ETIM

ETIM 2.0	EC001121
ETIM 3.0	EC002062
ETIM 4.0	EC002062
ETIM 5.0	EC002062


UNSPSC

UNSPSC 6.01	31251501
UNSPSC 7.0901	31251501
UNSPSC 11	31251501
UNSPSC 12.01	31251501
UNSPSC 13.2	31251501

Drawings

Valve connectors - SACC-V-4CON-PG7/C-3+PE - 1511967

Dimensioned drawing



Circuit diagram

