

Sensor/Actuator cable - SAC-4P- 5,0-170/M 8SIFS SO - 1539305

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Sensor/Actuator cable, 4-position, PUR, Black-gray RAL 7021, Free cable end, on Socket straight M8, Cable length: 5 m

Key commercial data

package_quantity	1
GTIN	4046356079310

Technical data

Dimensions

Length of cable	5 m
------------------------	-----

General

Number of positions	4
Coding	A - standard

Cable

Cable type	PUR halogen-free black
Cable abbreviation	Li9Y11Y-HF
Conductor cross section	0.25 mm ²
AWG signal line	24
Conductor structure signal line	32x 0.10 mm
Core diameter including insulation	1.15 mm ±0.05 mm
Thickness, insulation	≥ 0.38 mm (Core insulation)
Wire colors	brown, blue, black
Overall twist	3 wires, twisted
External sheath, color	Black-gray RAL 7021
External cable diameter	4.40 mm
Smallest bending radius, movable installation	44 mm
Number of bending cycles	4000000
Bending radius	44 mm
Traversing path	10 m
Traversing rate	3 m/s
Cable weight	23 kg/km
Outer sheath, material	PUR
Material conductor insulation	PP

Sensor/Actuator cable - SAC-4P- 5,0-170/M 8SIFS SO - 1539305

Technical data

Cable

Conductor material	Bare Cu litz wires
Insulation resistance	≥ 100 GΩ*km
Conductor resistance	≤ 77.6 Ω/m
Nominal voltage, cable	300 V
Test voltage, cable	4000 V

classifications

eCl@ss

eCl@ss 4.0	27060306
eCl@ss 4.1	27060306
eCl@ss 5.0	27061801
eCl@ss 5.1	27061801
eCl@ss 6.0	27061801
eCl@ss 7.0	27061801
eCl@ss 8.0	27061801

ETIM

ETIM 3.0	EC001855
ETIM 4.0	EC001855
ETIM 5.0	EC001855


UNSPSC

UNSPSC 6.01	31251501
UNSPSC 7.0901	31251501
UNSPSC 11	31251501
UNSPSC 12.01	31251501
UNSPSC 13.2	31251501

approvals


UL Listed / cUL Listed / cULus Listed /


Approval details

UL Listed 	
Nominal voltage UN	125 V
Nominal current IN	4 A
mm ² /AWG/kcmil	

Sensor/Actuator cable - SAC-4P- 5,0-170/M 8SIFS SO - 1539305

approvals

cUL Listed 	
Nominal voltage UN	125 V
Nominal current IN	4 A
mm ² /AWG/kcmil	

cULus Listed 	
--	--

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>