

Housing screw connection - SACC-M12-SCO NUT - 1552243

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



M12 SPEEDCON housing screw connection for M12 female inserts, with O-ring, for all SPEEDCON-capable THR and wave soldering contact carriers



Key commercial data

package_quantity	60
GTIN	4046356162111

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
---------------------------------	------------------

General

Mounting type	M12 x 1
---------------	---------

Material

Material, knurls	Nickel-plated brass
Material	Zinc die-cast (nickel-plated)
Sealing material	EPDM

classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27143423
eCl@ss 5.1	27143423
eCl@ss 6.0	27143423
eCl@ss 7.0	27449001
eCl@ss 8.0	27449001

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002350
ETIM 5.0	EC002350

Housing screw connection - SACC-M12-SCO NUT - 1552243

classifications

UNSPSC

UNSPSC 6.01	31251501
UNSPSC 7.0901	31251501
UNSPSC 11	31251501
UNSPSC 12.01	31251501
UNSPSC 13.2	31251501

approvals

GOST / GOST /

Approval details



Drawings

Dimensioned drawing



