

Coupler connector - CA-17F1N8A9504 - 1619995

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Coupling connector, straight, shielded: Yes, SPEEDCON locking, M23, Number of positions: 17, Type of contact: Socket, Crimp connection, Cable diameter: 10 mm ... 14.5 mm

The figure shows the 12-pos. product version

Key commercial data

package_quantity	1
GTIN	4046356819992

classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	272607xx
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260702
eCl@ss 7.0	27440102
eCl@ss 8.0	27440102

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002635
ETIM 5.0	EC002635


UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	43201404

Drawings

Coupler connector - CA-17F1N8A9504 - 1619995

Dimensioned drawing



Coupler connector - CA-17F1N8A9504 - 1619995

Schematic diagram

