

Cable gland - KV-M-M50-GD-(2X6) - 1636525

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



HEAVYCON M50 cable screw connection, metal, panel feed-through for data plug, with separable grommet, 2 x 6 mm hole diameter; inside diameter 37 mm

Key commercial data

package_quantity	5
GTIN	4046356028257

Technical data

Dimensions

Wrench size, union nut	50 mm
Wrench size, support	54 mm
Length of the connecting thread	10.00 mm
External cable diameter	5.5 mm ... 6 mm (Cable 1)
External cable diameter	5.5 mm ... 6 mm (Cable 2)
Conductor sealing range	5.50 mm ... 6.00 mm

Ambient conditions

Degree of protection	IP65
Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

General

Cable gland material	Nickel-plated brass
Material, pressure screw	Nickel-plated brass
Seal material	TPE
Material, O-ring	NBR
Thread type on connection side	M50

classifications

eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	27149109
eCl@ss 5.1	27149109

Cable gland - KV-M-M50-GD-(2X6) - 1636525

classifications

eCl@ss

eCl@ss 6.0	27149109
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109

ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441
ETIM 4.0	EC000441
ETIM 5.0	EC000441


UNSPSC

UNSPSC 6.01	30211808
UNSPSC 7.0901	39121408
UNSPSC 11	39121408
UNSPSC 12.01	39121408
UNSPSC 13.2	39121408

Drawings

Cable gland - KV-M-M50-GD-(2X6) - 1636525

Dimensioned drawing



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>