

Cable feed-through sleeve - HC-KDT 14-15 - 1644148

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Cable feed-through sleeves, for conductor diameters of 14-15 mm, starting at 10 mm, a cable binder can be used as strain relief

Key commercial data

package_quantity	10
GTIN	4017918896003

Technical data

Ambient conditions

Degree of protection	IP54
Ambient temperature (operation)	-40 °C ... 125 °C

General

Material	Thermoplastic rubber
Inflammability class according to UL 94	HB

classifications

eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	27149109
eCl@ss 5.1	27149109
eCl@ss 6.0	27149109
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109

ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441
ETIM 4.0	EC000441
ETIM 5.0	EC000441

UNSPSC

UNSPSC 6.01	30211808
UNSPSC 7.0901	39121408

Cable feed-through sleeve - HC-KDT 14-15 - 1644148

classifications

UNSPSC

UNSPSC 11	39121408
UNSPSC 12.01	39121408
UNSPSC 13.2	39121408

Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>