

Cable gland - HC-M-KV-T-M20 - 1646188

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Metal screw connection with cable bend protection and strain relief, thread length: 6 mm, cable sealing area: 7.5 - 15 mm, clamping area: 10 - 16 mm, SW 24, screw connection: M20

Key commercial data

package_quantity	10
GTIN	4017918941321

Technical data

Dimensions

Wrench size, union nut	24 mm
Wrench size, support	24 mm
Length of the connecting thread	6 mm
External cable diameter	7.5 mm ... 15 mm
Conductor sealing range	7.50 mm ... 15.00 mm
Clamping range of the strain relief clip	10.00 mm ... 16.00 mm

Ambient conditions

Degree of protection	IP65
Degree of protection	IP65
Ambient temperature (operation)	-20 °C ... 80 °C

General

Cable gland material	Nickel-plated brass
Material, pressure screw	Nickel-plated brass
Cable seal material	Perbunan
Material, O-ring	NBR
Thread type on connection side	M20
Color	silver

classifications

eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	27149109

Cable gland - HC-M-KV-T-M20 - 1646188

classifications

eCl@ss

eCl@ss 5.1	27149109
eCl@ss 6.0	27149109
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109

ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441
ETIM 4.0	EC000441
ETIM 5.0	EC000441


UNSPSC

UNSPSC 6.01	30211808
UNSPSC 7.0901	39121408
UNSPSC 11	39121408
UNSPSC 12.01	39121408
UNSPSC 13.2	39121408

Drawings

Cable gland - HC-M-KV-T-M20 - 1646188

Dimensioned drawing



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>