

Pressure screw set - HC-M-DE-M32 - 1647983

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Pressure screw set, for housing with M32 thread and glands, consisting of notched seal, 2 washers and pressure screw, cable diameter 16 - 25 mm, SW 32

Key commercial data

package_quantity	10
GTIN	4017918985134

Technical data

Dimensions

Wrench size, union nut	32 mm
External cable diameter	16 mm ... 25 mm
Conductor sealing range	16.00 mm ... 25.00 mm

Ambient conditions

Degree of protection	IP65
Degree of protection	IP54
Ambient temperature (operation)	-20 °C ... 80 °C

General

Material, pressure screw	Nickel-plated brass
Cable seal material	Perbunan
Thread type on connection side	M32

classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440209

ETIM

ETIM 2.0	EC001121
-----------------	----------

Pressure screw set - HC-M-DE-M32 - 1647983

classifications

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC001121
ETIM 5.0	EC000814

UNSPSC

UNSPSC 6.01	30211817
UNSPSC 7.0901	39121416
UNSPSC 11	43172601
UNSPSC 12.01	39121522
UNSPSC 13.2	39121522

Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>