

Interface module - FLKM 34 - 2281063

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



VARIOFACE module, with screw connection and flat-ribbon cable connector, for mounting on NS 32 or NS 35/7.5, with pin strip and short and long locking latches for socket strips, 34-pos.

The illustration shows a 40-position version



Key commercial data

package_quantity	5
GTIN	4017918054519

Technical data

Dimensions

Width	90 mm
Height	77 mm
Depth	58.5 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Nominal voltage U_N	< 50 V AC
Nominal voltage U_N	60 V DC
Max. current carrying capacity per branch	1 A
Number of positions	34
Test voltage	500 V (50 Hz, 1 min.)
Mounting position	Any
Standards/regulations	IEC 60664
Standards/regulations	DIN EN 50178
Standards/regulations	IEC 62103
Pollution degree	2
Surge voltage category	II

Connection data for connection 1

Connection name	PCB connection
-----------------	----------------

Interface module - FLKM 34 - 2281063

Technical data

Connection data for connection 1

Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Stripping length	8 mm
Screw thread	M3

classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152

ETIM

ETIM 2.0	EC001434
ETIM 3.0	EC001604
ETIM 4.0	EC001604
ETIM 5.0	EC002780

UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

approvals

UL Recognized / cUL Recognized / GOST / cULus Recognized /



Approval details

Interface module - FLKM 34 - 2281063

approvals

UL Recognized	
Nominal voltage UN	125 V
Nominal current IN	1 A
mm ² /AWG/kcmil	30-12

cUL Recognized	
Nominal voltage UN	125 V
Nominal current IN	1 A
mm ² /AWG/kcmil	30-12



accessories

System cable

FLK 34/EZ-DR/ 50/KONFEK - 2299479



FLK 34/EZ-DR/ 100/KONFEK - 2299482



Interface module - FLKM 34 - 2281063

accessories

FLK 34/EZ-DR/ 150/KONFEK - 2299495



FLK 34/EZ-DR/ 200/KONFEK - 2299505



FLK 34/EZ-DR/ 300/KONFEK - 2299518



FLK 34/EZ-DR/ 400/KONFEK - 2299521



FLK 34/EZ-DR/ 600/KONFEK - 2299534



FLK 34/EZ-DR/ 800/KONFEK - 2299547



Interface module - FLKM 34 - 2281063

accessories

FLK 34/EZ-DR/1000/KONFEK - 2299550



FLK EZ-DR.../.../... - 2295059



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>