

Interface module - FLKMS 34 - 2281571

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid
(<http://download.phoenixcontact.com>)



VARIOFACE module, with screw connection and flat-ribbon cable connector, for mounting on NS 32 or NS 35/7.5, with pin strip and short and long locking latches for socket strips, 34-pos.

The illustration shows a 50-pos. version



Key commercial data

package_quantity	5
GTIN	4017918054823

Technical data

Dimensions

Width	79 mm
Height	77 mm
Depth	72 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Nominal voltage U_N	< 50 V AC
Nominal voltage U_N	60 V DC
Max. current carrying capacity per branch	1 A
Number of positions	34
Test voltage	500 V (50 Hz, 1 min.)
Mounting position	Any
Standards/regulations	IEC 60664
Standards/regulations	DIN EN 50178
Standards/regulations	IEC 62103

Connection data for connection 1

Connection name	PCB connection
Connection in acc. with standard	IEC / EN
Connection method	Screw connection

Interface module - FLKMS 34 - 2281571

Technical data

Connection data for connection 1

Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Stripping length	8 mm
Screw thread	M3

classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152

ETIM

ETIM 2.0	EC001434
ETIM 3.0	EC001604
ETIM 4.0	EC001604
ETIM 5.0	EC002780

UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

approvals

GOST /

Approval details



Interface module - FLKMS 34 - 2281571

accessories

System cable

FLK 34/EZ-DR/ 50/KONFEK - 2299479



FLK 34/EZ-DR/ 100/KONFEK - 2299482



FLK 34/EZ-DR/ 150/KONFEK - 2299495



FLK 34/EZ-DR/ 200/KONFEK - 2299505



FLK 34/EZ-DR/ 300/KONFEK - 2299518



Interface module - FLKMS 34 - 2281571

accessories

FLK 34/EZ-DR/ 400/KONFEK - 2299521



FLK 34/EZ-DR/ 600/KONFEK - 2299534



FLK 34/EZ-DR/ 800/KONFEK - 2299547



FLK 34/EZ-DR/1000/KONFEK - 2299550



FLK EZ-DR.../.../... - 2295059



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>