

Interface module - FLKMS-D25 SUB/S (1-25) - 2294322

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



VARIOFACE module, with screw connection and D-Subminiature pin strip, for mounting on NS 35/7.5 or NS 32, 25-pos.

The illustration shows version FLKMS-D37 SUB/S (1-37)



Key commercial data

| | |
|------------------|---------------|
| package_quantity | 5 |
| GTIN | 4017918132705 |

Technical data

Dimensions

| | |
|--------|---------|
| Width | 67.5 mm |
| Height | 77 mm |
| Depth | 72 mm |

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |

General

| | |
|---|-----------------------|
| Nominal voltage U_N | 125 V AC/DC |
| Max. current carrying capacity per branch | 2.5 A |
| Number of positions | 25 |
| Status display | No |
| Test voltage | 800 V (50 Hz, 1 min.) |
| Mounting position | Any |
| Standards/regulations | IEC 60664 |
| Standards/regulations | DIN EN 50178 |
| Standards/regulations | IEC 62103 |
| Pollution degree | 2 |
| Surge voltage category | II |

Connection data for connection 1

| | |
|-----------------|----------------|
| Connection name | PCB connection |
|-----------------|----------------|

Interface module - FLKMS-D25 SUB/S (1-25) - 2294322

Technical data

Connection data for connection 1

| | |
|--|---------------------|
| Connection in acc. with standard | IEC / EN |
| Connection method | Screw connection |
| Conductor cross section solid min. | 0.2 mm ² |
| Conductor cross section solid max. | 4 mm ² |
| Conductor cross section stranded min. | 0.2 mm ² |
| Conductor cross section stranded max. | 2.5 mm ² |
| Conductor cross section AWG/kcmil min. | 24 |
| Conductor cross section AWG/kcmil max | 12 |
| Stripping length | 8 mm |
| Screw thread | M3 |

classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27250313 |
| eCl@ss 4.1 | 27250313 |
| eCl@ss 5.0 | 27250313 |
| eCl@ss 5.1 | 27250313 |
| eCl@ss 6.0 | 27242608 |
| eCl@ss 7.0 | 27141152 |
| eCl@ss 8.0 | 27141152 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC001434 |
| ETIM 3.0 | EC001604 |
| ETIM 4.0 | EC001604 |
| ETIM 5.0 | EC002780 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211824 |
| UNSPSC 7.0901 | 39121421 |
| UNSPSC 11 | 39121421 |
| UNSPSC 12.01 | 39121421 |
| UNSPSC 13.2 | 39121421 |

approvals

GOST /

Approval details

Interface module - FLKMS-D25 SUB/S (1-25) - 2294322

approvals



accessories

System cable

CABLE-D25SUB/B/S/ 50/KONFEK/S - 2302120



CABLE-D25SUB/B/S/100/KONFEK/S - 2302133



CABLE-D25SUB/B/S/150/KONFEK/S - 2302146



CABLE-D25SUB/B/S/200/KONFEK/S - 2302159



CABLE-D25SUB/B/S/300/KONFEK/S - 2302162



Interface module - FLKMS-D25 SUB/S (1-25) - 2294322

accessories

CABLE-D25SUB/B/S/400/KONFEK/S - 2302175



CABLE-D25SUB/B/S/600/KONFEK/S - 2302188



CABLE D-SUB-S/.../.../... - 2302340



CABLE D-SUB-B-B-S/.../.../... - 2302421



CABLE-D-25SUB/F/OE/0,25/S/0,5M - 2926153



Interface module - FLKMS-D25 SUB/S (1-25) - 2294322

accessories

CABLE-D-25SUB/F/OE/0,25/S/1,0M - 2926166



CABLE-D-25SUB/F/OE/0,25/S/1,5M - 2926179



CABLE-D-25SUB/F/OE/0,25/S/2,0M - 2926182



CABLE-D-25SUB/F/OE/0,25/S/3,0M - 2926195



CABLE-D-25SUB/F/OE/0,25/S/4,0M - 2926205



CABLE-D-25SUB/F/OE/0,25/S/6,0M - 2926218



Interface module - FLKMS-D25 SUB/S (1-25) - 2294322

accessories

CABLE-D-25SUB-F-OE-0,25-S/... - 2900906



Drawings

Schematic diagram

