

Cable - CABLE-D15SUB/B/S/200/KONFEK/S - 2302081

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Round shielded cable set, with 15-pos. D-SUB female and male connectors, cable length: 2 m

Key commercial data

package_quantity	1
GTIN	4017918893040

Technical data

General

Nominal voltage U_N	125 V AC/DC
Max. current carrying capacity per path	2 A
Max. conductor resistance	$\leq 0.09 \Omega/\text{m}$
Length of cable	2 m
Single wire, cross section	0.25 mm ²
AWG	24
External diameter	9 mm
Shielding	yes
Shielding	Tinned copper-braided shield, approx. 85% covering
Insertion/withdrawal cycles	> 200

Environmental conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Flame resistance	IEC 60332-1

Connector, module side

Number of positions	15
Connectors	D-SUB socket strip
Number of plugs	1

Connector, controller side

Number of positions	15
Connectors	D-SUB pin strip
Number of plugs	1

Cable - CABLE-D15SUB/B/S/200/KONFEK/S - 2302081

classifications

eCl@ss

eCl@ss 4.0	27060306
eCl@ss 4.1	27060306
eCl@ss 5.0	27061801
eCl@ss 5.1	27061801
eCl@ss 6.0	27061801
eCl@ss 7.0	27061801
eCl@ss 8.0	27061801

ETIM

ETIM 2.0	EC000237
ETIM 3.0	EC000237
ETIM 4.0	EC000237
ETIM 5.0	EC000830

UNSPSC

UNSPSC 6.01	26121620
UNSPSC 7.0901	26121620
UNSPSC 11	26121620
UNSPSC 12.01	26121620
UNSPSC 13.2	26121620

approvals

UL Recognized / cUL Recognized / GOST / cULus Recognized /

Approval details

UL Recognized 

cUL Recognized 
--

GOST 
--

cULus Recognized 
--

Cable - CABLE-D15SUB/B/S/200/KONFEK/S - 2302081

Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>