

Basic terminal block - URELG 4-PMTK - 2820712

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Basic termination blocks with test connection on both sides and knife disconnection for NS 32 and NS 35/7.5 DIN rail, with end cover, for ST-REL..., ST-OV... and ST-OE... plugs, 4-pos.

The illustration shows versions with a different no. of positions

Key commercial data

package_quantity	10
GTIN	4017918076849

Technical data

Dimensions

Width	27 mm
Height	86.5 mm
Depth	109.5 mm

General

Number of positions	4
Nominal voltage U_N	400 V (voltage is determined by the coupling connector.)
Nominal current I_N	16 A (current is determined by the coupling connector.)
Color	gray
Insulating material	PA

Connection data

Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	4 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Connection method	Screw connection
Stripping length	7 mm
Screw thread	M3

classifications

eCl@ss

Basic terminal block - URELG 4-PMTK - 2820712

classifications

eCl@ss

eCl@ss 4.0	27141127
eCl@ss 4.1	27141127
eCl@ss 5.0	27371603
eCl@ss 5.1	27371603
eCl@ss 6.0	27371603
eCl@ss 7.0	27371603
eCl@ss 8.0	27371603

ETIM

ETIM 2.0	EC001456
ETIM 3.0	EC001456
ETIM 4.0	EC001456
ETIM 5.0	EC001456


UNSPSC


UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

CSA / UL Recognized / cUL Recognized / GOST / DNV / cULus Recognized /

Approval details




	
Nominal voltage UN	300 V
Nominal current IN	11 A
mm ² /AWG/kcmil	28-12

	
Nominal voltage UN	300 V
Nominal current IN	10 A
mm ² /AWG/kcmil	30-12

Basic terminal block - URELG 4-PMTK - 2820712

approvals

cUL Recognized	
Nominal voltage UN	300 V
Nominal current IN	10 A
mm ² /AWG/kcmil	30-12



accessories

End block

E/UK - 1201442



Bridge

FB-150 METER - 0201595



Basic terminal block - URELG 4-PMTK - 2820712

accessories

VS - 3004207




DB 50- 90 BU - 2821180



DB 50- 90 GY - 2820929



DB 50- 90 BK - 2820916



KB RELG 7 - 2961095



KB RELG 4 - 2961082



Basic terminal block - URELG 4-PMTK - 2820712

accessories

KB RELG 3 - 2961079



KB RELG 2 - 2961066



Mounting material

ZSR - 2303608



Test plug terminal block


RPS - 0201647




Drawings

Basic terminal block - URELG 4-PMTK - 2820712

Dimensioned drawing



Schematic diagram




1 - 3

1-3 = fixed bridge, cross connection rail, spacer

Basic terminal block - URELG 4-PMTK - 2820712

Schematic diagram



1 = Coupling connector
2 = Coding
3 = Cover
4 = Basic termination block

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>