

Electronic housing - UM122-SEMFE-A92 - 2909442

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Lateral element, to attach profile cover UM 122 to DIN rail NS 35/7.5, with M3 screw fixture, tightening torque 0.5 Nm ... 0.6 Nm

Product Features

- Inexpensive as a result of reducing the number of separate housing parts
- Wide range of options for external conductor connection
- Flexible size and shape
- High degree of mechanical stability by screwing the lateral elements to the profile
- Can be snapped onto standard NS 35/7,5 and NS 35/15 DIN rails

Key commercial data

package_quantity	10
GTIN	4017918171681

Technical data

General

Housing type	Side cover
Color	green

classifications

eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506
eCl@ss 6.0	27180802
eCl@ss 7.0	27182701
eCl@ss 8.0	27182701

ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC000721

Electronic housing - UM122-SEMFE-A92 - 2909442

classifications

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

approvals

UL Recognized /

Approval details



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>