

Interface module - UM 45-FLK26 - 2962586

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



VARIOFACE module, with screw connection and flat-ribbon cable connector, for assembly on NS 35/7.5, 26 positions

The illustration shows a 34-position version



Key commercial data

package_quantity	1
GTIN	4017918087258

Technical data

Dimensions

Width	90 mm
Height	45 mm
Depth	50 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Nominal voltage U_N	25 V AC
Nominal voltage U_N	60 V DC
Max. current carrying capacity per branch	1 A
Number of positions	26
Test voltage input/output	500 V AC
Mounting position	Any
Standards/regulations	IEC 60664
Standards/regulations	DIN VDE 0110
Standards/regulations	DIN VDE 110
Pollution degree	2
Surge voltage category	II

Connection data for connection 1

Connection name	PCB connection
-----------------	----------------

Interface module - UM 45-FLK26 - 2962586

Technical data

Connection data for connection 1

Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Conductor cross section solid min.	0.14 mm ²
Conductor cross section solid max.	1.5 mm ²
Conductor cross section stranded min.	0.14 mm ²
Conductor cross section stranded max.	1.5 mm ²
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	16
Stripping length	6 mm
Screw thread	M3

classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152

ETIM

ETIM 2.0	EC001434
ETIM 3.0	EC001604
ETIM 4.0	EC001604
ETIM 5.0	EC002780

UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

approvals

UL Recognized / cUL Recognized / GOST / cULus Recognized /



Approval details

Interface module - UM 45-FLK26 - 2962586

approvals

UL Recognized	
Nominal voltage UN	125 V
Nominal current IN	1 A
mm ² /AWG/kcmil	

cUL Recognized	
Nominal voltage UN	125 V
Nominal current IN	1 A
mm ² /AWG/kcmil	



accessories

System cable

FLK 26/EZ-DR/ 50/KONFEK - 2299385



FLK 26/EZ-DR/ 100/KONFEK - 2299398



Interface module - UM 45-FLK26 - 2962586

accessories

FLK 26/EZ-DR/ 150/KONFEK - 2299408



FLK 26/EZ-DR/ 300/KONFEK - 2299424



FLK 26/EZ-DR/ 400/KONFEK - 2299437



FLK 26/EZ-DR/ 600/KONFEK - 2299440



FLK 26/EZ-DR/ 800/KONFEK - 2299453



FLK 26/EZ-DR/1000/KONFEK - 2299466



Interface module - UM 45-FLK26 - 2962586

accessories

FLK EZ-DR.../.../... - 2295059



Drawings

Circuit diagram

