

Feed-through terminal block - UK 10 - 3005015

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Feed-through terminal block, Connection method: Screw connection, Cross section: 0.5 mm² - 10 mm², AWG: 20 - 8, Width: 8.2 mm, Color: gray, Mounting type: NS 35/7,5, NS 35/15

Key commercial data

package_quantity	50
GTIN	4017918090982

Technical data

General

Number of levels	1
Number of connections	2
Color	gray
Insulating material	PA
Inflammability class according to UL 94	V0

General

Rated surge voltage	8 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC / EN
Nominal current I _N	57 A
Nominal voltage U _N	800 V
Open side panel	ja

Dimensions

Width	8.2 mm
Length	42.5 mm
Height NS 35/7,5	47 mm
Height NS 35/15	54.5 mm
Height NS 32	52 mm

Connection data

Conductor cross section solid min.	0.5 mm ²
Conductor cross section solid max.	10 mm ²

Feed-through terminal block - UK 10 - 3005015

Technical data

Connection data

Conductor cross section AWG/kcmil min.	20
Conductor cross section AWG/kcmil max	8
Conductor cross section stranded min.	0.5 mm ²
Conductor cross section stranded max.	6 mm ²
Min. AWG conductor cross section, stranded	20
Max. AWG conductor cross section, stranded	10
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.5 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	6 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.5 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	4 mm ²
2 conductors with same cross section, solid min.	0.5 mm ²
2 conductors with same cross section, solid max.	2.5 mm ²
2 conductors with same cross section, stranded min.	0.5 mm ²
2 conductors with same cross section, stranded max.	2.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	4 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.5 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	2.5 mm ²
Cross section with insertion bridge, solid max.	6 mm ²
Cross section with insertion bridge, stranded max.	6 mm ²
Connection method	Screw connection
Stripping length	10 mm
Internal cylindrical gage	A5
Screw thread	M4
Tightening torque, min	1.5 Nm
Tightening torque max	1.8 Nm

classifications

eCl@ss

eCl@ss 4.0	27141120
eCl@ss 4.1	27141120
eCl@ss 5.0	27141120
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120

Feed-through terminal block - UK 10 - 3005015

classifications

eCl@ss

eCl@ss 8.0	27141120
------------	----------

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000897
ETIM 5.0	EC000897


UNSPSC


UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410


approvals

CSA / UL Recognized / cUL Recognized / GOST / GL / BV / DNV / RS / KR / NK / GOST / cULus Recognized / BV /

Approval details

	
Nominal voltage UN	600 V
Nominal current IN	55 A
mm ² /AWG/kcmil	26-8









	
Nominal voltage UN	600 V
Nominal current IN	50 A
mm ² /AWG/kcmil	26-8

	
Nominal voltage UN	600 V
Nominal current IN	50 A

Feed-through terminal block - UK 10 - 3005015

approvals

mm ² /AWG/kcmil	26-8
----------------------------	------



accessories

End cover

D-UK 4/10 - 3003020



Feed-through terminal block - UK 10 - 3005015

accessories

D-UK 4/10 BU - 3003101



Warning label printed

WS 5- 8 - 1004416



WS 4- 8 - 1004212



WS 3- 8 - 1004128



Cover profile

EA 5-WS - 1024085



Feed-through terminal block - UK 10 - 3005015

accessories

EA 5 - 1024014



Short-circuit connector

KSS 8 - 0311540



Bridge

STL 35/10 - 0204084



STL 16/10 - 0204518



FBI 2- 8 - 0200020



Feed-through terminal block - UK 10 - 3005015

accessories

FBI 4- 8 - 0200046



FBI 10- 8 - 0203263



FBI 3- 8 - 0200059



EB 2- 8 - 0202154



EB 3- 8 - 0202141



EB 10- 8 - 0202138



Feed-through terminal block - UK 10 - 3005015

accessories

SBJ 2- 8/13 - 0303286



SB 2- 8/13 - 0202235



EB 4- 8 - 0202142



Partition plate

TS-K - 1302215



Partition plate

ATP-UK - 3003224



Insulating sleeve

Feed-through terminal block - UK 10 - 3005015

accessories

IS-K 10 - 1303337



ISSBI 10- 8 - 0301534



Mounting rail

NS 32 PERF 2000MM - 1201002



NS 32 UNPERF 2000MM - 1201015



NS 35/ 7,5 PERF 2000MM - 0801733



Feed-through terminal block - UK 10 - 3005015

accessories

NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



Feed-through terminal block - UK 10 - 3005015

accessories

NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



Feed-through terminal block - UK 10 - 3005015

accessories

NS 35/15 WH UNPERF 2000MM - 1204135



NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



Feed-through terminal block - UK 10 - 3005015

accessories

NS 35/15-2,3 UNPERF 2000MM - 1201798



Terminal marking

ZB 8:UNBEDRUCKT - 1052002



UC-TM 8 - 0818072



UCT-TM 8 - 0828740



Labeled terminal marker

ZB 8 CUS - 0825011



Feed-through terminal block - UK 10 - 3005015

accessories

UC-TM 8 CUS - 0824597



UCT-TM 8 CUS - 0829616



End block

CLIPFIX 35 - 3022218



CLIPFIX 35-5 - 3022276



E/NS 35 N - 0800886



Feed-through terminal block - UK 10 - 3005015

accessories

E/UK - 1201442



E/UK 1 - 1201413



Test socket

PSBJ 4/15/6 FARBLOS - 0303419



PSBJ 4/15/6 WH - 0303312



PSBJ 4/15/6 RD - 0303325



Feed-through terminal block - UK 10 - 3005015

accessories

PSBJ 4/15/6 BU - 0303354



PSBJ 4/15/6 YE - 0303367



PSBJ 4/15/6 GN - 0303370



PSBJ 4/15/6 VT - 0303383



PSBJ 4/15/6 GY - 0303396



PSBJ 4/15/6 BK - 0303406



Feed-through terminal block - UK 10 - 3005015

accessories

PSB 4/7/6 - 0303299



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>