

Knife disconnect terminal block - ZDMTK 2,5 BU - 3006784

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Knife disconnect terminal block, Connection type: Spring-cage connection, Cross section: 0.2 mm² - 4 mm², AWG: 24 - 12, Nominal current: 16 A, Nominal voltage: 400 V, Length: 107 mm, Width: 6.2 mm, Color: blue, Assembly: NS 35/7,5, NS 35/15

The figure shows a version of the article

Product Features

- Disconnect knife for one level

Key commercial data

package_quantity	50
GTIN	4017918147174

Technical data

General

Number of levels	2
Number of connections	4
Color	blue
Insulating material	PA
Inflammability class according to UL 94	V0

General

Maximum load current	20 A (with 4 mm ² conductor cross section)
Rated surge voltage	6 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-1
Nominal current I _N	16 A (the maximum load current must not be exceeded by the total current of all connected conductors)
Nominal voltage U _N	400 V
Open side panel	nein

Dimensions

Width	6.2 mm
Length	107 mm
Height NS 35/7,5	55 mm

Knife disconnect terminal block - ZDMTK 2,5 BU - 3006784

Technical data

Dimensions

Height NS 35/15	62.5 mm
-----------------	---------

Connection data

Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	2.5 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	2.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	0.5 mm ²
Connection method	Spring-cage connection

classifications

eCl@ss

eCl@ss 4.0	27141117
eCl@ss 4.1	27141117
eCl@ss 5.0	27141120
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

ETIM

ETIM 2.0	EC000902
ETIM 3.0	EC000902
ETIM 4.0	EC000902
ETIM 5.0	EC000902

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Knife disconnect terminal block - ZDMTK 2,5 BU - 3006784

approvals

UL Recognized / cUL Recognized / PRS / cULus Recognized /

Approval details

UL Recognized	
Nominal voltage UN	300 V
Nominal current IN	10 A
mm ² /AWG/kcmil	26-12

cUL Recognized	
Nominal voltage UN	300 V
Nominal current IN	10 A
mm ² /AWG/kcmil	26-12

PRS

cULus Recognized

accessories

Partition plate

ATP-ZFKKB 4 - 3005772



Screwdriver tools

Knife disconnect terminal block - ZDMTK 2,5 BU - 3006784

accessories

SZF 1-0,6X3,5 - 1204517



Labeled terminal marker

BN-ZB 5,2/WH CUS - 0824271



ZBF 6 CUS - 0825027



UC-TMF 6 CUS - 0824646



UCT-TMF 6 CUS - 0829665



Mounting rail

Knife disconnect terminal block - ZDMTK 2,5 BU - 3006784

accessories

NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



Knife disconnect terminal block - ZDMTK 2,5 BU - 3006784

accessories

NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



Knife disconnect terminal block - ZDMTK 2,5 BU - 3006784

accessories

NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



Knife disconnect terminal block - ZDMTK 2,5 BU - 3006784

accessories

NS 35/15 CAP - 1206573



NS 35/15-2,3 UNPERF 2000MM - 1201798



Terminal marking

ZBF 6:UNBEDRUCKT - 0808710



UC-TMF 6 - 0818140



UCT-TMF 6 - 0828746



Insulating sleeve

Knife disconnect terminal block - ZDMTK 2,5 BU - 3006784

accessories

ISH 2,5/0,2 - 3002843



ISH 2,5/0,5 - 3002856



ISH 2,5/1,0 - 3002869



End block

CLIPFIX 35 - 3022218



CLIPFIX 35-5 - 3022276



Knife disconnect terminal block - ZDMTK 2,5 BU - 3006784

accessories

E/NS 35 N - 0800886



E/UK - 1201442



E/UK 1 - 1201413



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>