

Marker pin Zack strip - BN-ZB 7,5/ WH-100:UNBEDRUCKT - 5060854

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Marker pin Zack strip, Strip, white, Unlabeled, Can be labeled with: Plotter, Mounting type: Plug in, For terminal block width: 7.5 mm, Lettering field: 6 x 4 mm

The illustration shows version
BN-ZB 7,5 -UNPRINTED, -
CONSEC. NOS and BNB-ZB 7,5
SO/CMS

Key commercial data

package_quantity	100
GTIN	4017918096083

Technical data

Dimensions

Width (a)	6 mm
-----------	------

Ambient conditions

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-40 °C ... 100 °C

General

Note	Can be labeled with CMS
Color	white
Components	free from silicone and halogen
Inflammability class according to UL 94	V2
Material	PA
Number of individual labels	1000

classifications

eCl@ss

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137

Marker pin Zack strip - BN-ZB 7,5/ WH-100:UNBEDRUCKT - 5060854

classifications

eCl@ss

eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>