



RoHS  Compliant

[BOMcheck.net](https://www.bomcheck.net)

Color:

## Data

### Electrical data

Rated current (Ex e II)	12 A
-------------------------	------

### Ratings per IEC/EN 60664-1

Rated voltage (III / 3)	800 V
-------------------------	-------

Rated current	14 A
---------------	------

### Geometrical Data

Width	20 mm / 0.787 inch
-------	--------------------

Height	19 mm / 0.748 inch
--------	--------------------



Depth	4.1 mm / 0.161 inch
-------	---------------------

**Material Data**

Color	light gray
Fire load	0.014 MJ
Weight	1.727 g

**Commercial data**

Country of origin	DE
GTIN	4045454721879
Customs Tariff No.	85366990990
Product Group	22 (TOPJOB S)

**Downloads****Documentation****Bid Text**

2000-406	Oct 20, 2017	DOC 24.1 kB	Download
----------	--------------	----------------	----------

**smartDATA****CAD data**

3D Download 2000-406	URL	Download
----------------------	-----	----------

**Product family****TOPJOB® S**

TOPJOB® S: In various industrial applications and modern building installations, WAGO's wide and versatile range of rail-mount terminal blocks provides more than just reliable electrical connections.

[Learn more about the product family.](#)

[Show all products from the family](#)

Subject to changes.