



RoHS Compliant BOMcheck.net Color:

Data
Electrical data

Rated current (Ex e II)	12 A
-------------------------	------

Ratings per IEC/EN 60664-1

Rated voltage (III / 3)	800 V
Rated current	14 A

Geometrical Data

Width	27 mm / 1.063 inch
Height	19 mm / 0.748 inch



Depth	4.1 mm / 0.161 inch
-------	---------------------

Material Data

Color	light gray
Fire load	0.014 MJ
Weight	1.427 g

Commercial data

Country of origin	DE
GTIN	4045454721985
Customs Tariff No.	85366990990
Product Group	22 (TOPJOB S)

Downloads**Documentation****Bid Text**

2000-438	Oct 20, 2017	DOC 24.1 kB	Download
----------	--------------	----------------	----------

smartDATA**CAD data**

3D Download 2000-438	URL	Download
----------------------	-----	----------

Product family**TOPJOB® S**

TOPJOB® S: In various industrial applications and modern building installations, WAGO's wide and versatile range of rail-mount terminal blocks provides more than just reliable electrical connections.

[Learn more about the product family.](#)

[Show all products from the family](#)

Subject to changes.

WAGO Kontakttechnik GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.