



RoHS  Compliant

[BOMcheck.net](https://www.bomcheck.net)

Color:

## Data

### Electrical data

Rated current (Ex e II)	16 A
-------------------------	------

### Ratings per IEC/EN 60664-1

Rated voltage (III / 3)	800 V
-------------------------	-------

Rated current	18 A
---------------	------

### Geometrical Data

Width	28.1 mm / 1.106 inch
-------	----------------------



Height	19 mm / 0.748 inch
Depth	4.1 mm / 0.161 inch

### Material Data

Color	light gray
Fire load	0.015 MJ
Weight	1.629 g

### Commercial data

Packaging type	bag
Country of origin	DE
GTIN	4055143699662
Customs Tariff No.	85366990990
Product Group	22 (TOPJOB S)

### Downloads

#### Documentation

#### Bid Text

2001-437	Oct 20, 2017	DOC 24.1 kB	Download
----------	--------------	----------------	----------

### smartDATA

#### CAD data

3D Download 2001-437	URL	Download
----------------------	-----	----------



## Product family

### TOPJOB® S

TOPJOB® S: In various industrial applications and modern building installations, WAGO's wide and versatile range of rail-mount terminal blocks provides more than just reliable electrical connections.

[Learn more about the product family.](#)

[Show all products from the family](#)

Subject to changes.