

Data sheet | Item number: 2002-404/000-005

Push-in type jumper bar; insulated; 4-way; Nominal current 25 A

www.wago.com/2002-404/000-005



RoHS
Compliant

[BOMcheck.net](https://www.bomcheck.net)

Color: ■

Data

Electrical data

Rated current (Ex e II)

20 A

**Ratings per IEC/EN 60664-1**

Rated voltage (III / 3)	800 V
Rated current	25 A

Geometrical Data

Width	19.1 mm / 0.752 inch
Height	19 mm / 0.748 inch
Depth	4.1 mm / 0.161 inch

Material Data

Color	red
Fire load	0.014 MJ
Weight	1.908 g

Commercial data

Country of origin	DE
GTIN	4050821076018
Customs Tariff No.	85366990990

Downloads**Documentation****Bid Text**

2002-404/000-005	Oct 20, 2017	DOC 24.6 kB	Download
------------------	--------------	----------------	----------

smartDATA**CAD data**

3D Download 2002-404/000-005	URL	Download
------------------------------	-----	----------



Product family

TOPJOB® S

TOPJOB® S: In various industrial applications and modern building installations, WAGO's wide and versatile range of rail-mount terminal blocks provides more than just reliable electrical connections.

[Learn more about the product family.](#)

[Show all products from the family](#)

Subject to changes.