

Data sheet | Item number: 2002-404/000-006

Push-in type jumper bar; insulated; 4-way; Nominal current 25 A

www.wago.com/2002-404/000-006



RoHS Compliant

BOMcheck.net

Color: ■

Data

Electrical data

Rated current (Ex e II)

20 A

**Ratings per IEC/EN 60664-1**

| | |
|-------------------------|-------|
| Rated voltage (III / 3) | 800 V |
| Rated current | 25 A |

Geometrical Data

| | |
|--------|----------------------|
| Width | 19.1 mm / 0.752 inch |
| Height | 19 mm / 0.748 inch |
| Depth | 4.1 mm / 0.161 inch |

Material Data

| | |
|-----------|----------|
| Color | blue |
| Fire load | 0.014 MJ |
| Weight | 1.908 g |

Commercial data

| | |
|--------------------|---------------|
| Country of origin | DE |
| GTIN | 4050821077756 |
| Customs Tariff No. | 85366990990 |

Downloads**Documentation****Bid Text**

| | | | |
|------------------|--------------|----------------|----------|
| 2002-404/000-006 | Oct 20, 2017 | DOC 24.6 kB | Download |
|------------------|--------------|----------------|----------|

smartDATA**CAD data**

| | | |
|------------------------------|-----|----------|
| 3D Download 2002-404/000-006 | URL | Download |
|------------------------------|-----|----------|



Product family

TOPJOB® S

TOPJOB® S: In various industrial applications and modern building installations, WAGO's wide and versatile range of rail-mount terminal blocks provides more than just reliable electrical connections.

[Learn more about the product family.](#)

[Show all products from the family](#)

Subject to changes.