

Data sheet | Item number: 2002-409

Push-in type jumper bar; insulated; 9-way; Nominal current 25 A

www.wago.com/2002-409



RoHS Compliant

[BOMcheck.net](https://www.bomcheck.net)

Color:

Data

Electrical data

Rated current (Ex e II)	20 A
-------------------------	------

Ratings per IEC/EN 60664-1

Rated voltage (III / 3)	800 V
-------------------------	-------

Rated current	25 A
---------------	------

Geometrical Data

Width	45.2 mm / 1.78 inch
-------	---------------------

Height	19 mm / 0.748 inch
--------	--------------------

Depth	4.1 mm / 0.161 inch
-------	---------------------



Material Data

Color	light gray
Fire load	0.032 MJ
Weight	4.3 g

Commercial data

Country of origin	DE
GTIN	4017332999410
Customs Tariff No.	85366990990
Product Group	22 (TOPJOB S)

Downloads

Documentation

Bid Text

2002-409	Oct 25, 2017	DOC 24.1 kB	Download
----------	--------------	----------------	----------

smartDATA

CAD data

3D Download 2002-409	URL	Download
----------------------	-----	----------

Product family

TOPJOB® S

TOPJOB® S: In various industrial applications and modern building installations, WAGO's wide and versatile range of rail-mount terminal blocks provides more than just reliable electrical connections.

[Learn more about the product family.](#)

[Show all products from the family](#)

Subject to changes.