

**Data sheet | Item number: 2002-440**

Push-in type jumper bar; insulated; from 1 to 10; Nominal current 25 A

[www.wago.com/2002-440](http://www.wago.com/2002-440)



RoHS  Compliant

[BOMcheck.net](https://www.bomcheck.net)

Color:

**Data**

**Electrical data**

Rated current (Ex e II)	20 A
-------------------------	------

**Ratings per IEC/EN 60664-1**

Rated voltage (III / 3)	800 V
-------------------------	-------

Rated current	25 A
---------------	------

**Geometrical Data**

Width	50.4 mm / 1.984 inch
-------	----------------------



Height	19 mm / 0.748 inch
Depth	4.1 mm / 0.161 inch

**Material Data**

Color	light gray
Fire load	0.024 MJ
Weight	2.833 g

**Commercial data**

Country of origin	DE
GTIN	4017332999502
Customs Tariff No.	85366990990
Product Group	22 (TOPJOB S)

**Downloads****Documentation****Bid Text**

2002-440	Oct 25, 2017	DOC 24.6 kB	Download
----------	--------------	----------------	----------

**smartDATA****CAD data**

3D Download 2002-440	URL	Download
----------------------	-----	----------

**Product family****TOPJOB® S**

TOPJOB® S: In various industrial applications and modern building installations, WAGO's wide and versatile range of rail-mount terminal blocks provides more than just reliable electrical connections.

[Learn more about the product family.](#)

[Show all products from the family](#)

Subject to changes.