



ITEM-NO. (ITEM-NO.)	2091-1424
Measured voltage (Measured voltage / V)	160
Measured shock voltage (Measured shock voltage / kV)	2.5
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	10
RM (PIN SPACING / mm)	3.5
P (NO. OF POLES)	4
Height (Height / mm)	12.4
Width (Width / mm)	16
Depth (Depth / mm)	17.5
COLOR (COLOR)	lichtgrau
Comment (Comment)	$L = (\text{No. of poles} - 1) \times \text{Pin Spacing} + 5.5 \text{ mm}$
Dimensions (Dimensions)	1.2 +0.1 mm