



RoHS
Compliant

BOMcheck.net

Data

Connection data

| | |
|------------------|---|
| No. of poles | 2 |
| Number of levels | 1 |

Geometrical Data

| | |
|-----------------------------------|----------------------------|
| Pin spacing | 3.5 mm (0.138 inch) |
| Solder pin length | 3.5 mm |
| Solder pin diameter | 1 mm |
| Drilled hole diameter (tolerance) | 1.2 ^(+ 0.05) mm |

Plug connection

| | |
|------------------------------------|---------------------|
| Contact type (pluggable connector) | Male connector/plug |
| Connector connection type | for PCBs |



PCB contact

| | |
|-------------|-----|
| PCB contact | THT |
|-------------|-----|

Material Data

| | |
|--------|---------|
| Weight | 0.205 g |
|--------|---------|

Commercial data

| | |
|--------------------|---------------------|
| Country of origin | DE |
| GTIN | 4044918984096 |
| Customs Tariff No. | 85369010000 |
| Product Group | 4 (Printed Circuit) |

Subject to changes.

WAGO Kontakttechnik GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.