

Data sheet | Item number: 261-337/342-000

4-conductor terminal block; with push-buttons on both sides; with fixing flange; for screw or similar mounting types; Fixing hole 3.2 mm Ø; with 209-123 mounting carrier for DIN 35 rail

[www.wago.com/261-337/342-000](http://www.wago.com/261-337/342-000)





## Data

### Electrical data

#### Ratings per IEC/EN 60664-1

Legend (ratings)

(III / 3) ≙ Overvoltage category III / Pollution degree 3

### Connection data

|                                   |  |
|-----------------------------------|--|
| Connection technology             | CAGE CLAMP®                                  |
| Actuation type                    | Operating tool<br>Push-button                |
| Connectable conductor materials   | Copper<br>Aluminum                           |
| Solid conductor                   | 0.08 ... 2.5 mm <sup>2</sup> / 28 ... 14 AWG |
| Fine-stranded conductor           | 0.08 ... 2.5 mm <sup>2</sup> / 28 ... 14 AWG |
| Strip length                      | 8 ... 9 mm / 0.31 ... 0.35 Inch              |
| No. of poles                      | 1  |
| Total number of connection points | 4  |
| Total number of potentials        | 1  |
| Number of levels                  | 1  |
| Type of wiring                    | Side-entry wiring                            |

### Geometrical Data

|                         |                      |
|-------------------------|----------------------|
| Width                   | 10 mm / 0.394 inch   |
| Height from the surface | 23.2 mm / 0.913 inch |

|       |                    |
|-------|--------------------|
| Depth | 28 mm / 1.102 inch |
|-------|--------------------|

### Mechanical data

|               |                 |
|---------------|-----------------|
| Design        | horizontal      |
| Mounting type | Mounting flange |
| Marking level | Side marking    |

### Material Data

|           |              |
|-----------|--------------|
| Color     | green-yellow |
| Fire load | 0.078 MJ     |
| Weight    | 4.439 g      |

### Commercial data




|                    |               |
|--------------------|---------------|
| Country of origin  | DE            |
| GTIN               | 4044918614610 |
| Customs Tariff No. | 85369010000   |

### Approvals / Certificates

#### Country specific Approvals


| Logo   | Approval                        | Certificate name |
|--|---------------------------------|------------------|
|  | CCA<br>DEKRA Certification B.V. | NTR-NL 6509      |
|  | CCA<br>DEKRA Certification B.V. | 2110272.02       |

#### Ship Approvals


| Logo   | Approval                           | Certificate name |
|--|------------------------------------|------------------|
|  | ABS<br>American Bureau of Shipping | 14-HG1241539-PDA |
|  | LR<br>Lloyds Register              | 91/20242(E6)     |
|  | LR<br>Lloyds Register              | 91/20242 (E7)    |

## Compatible products


### Jumper


|  |   |  |
|--|---|--|
|  | <b>Item no.: 261-402</b><br>Comb-style jumper bar; insulated; 2-way; reduces conductor size to 1.5 mm | <a href="http://www.wago.com/261-402">www.wago.com/261-402</a> |
|--|---|--|


### assembling


|  |   |  |
|--|---|--|
|  | <b>Item no.: 209-137</b><br>Mounting adapter; can be used as end plate; 6.5 mm wide | <a href="http://www.wago.com/209-137">www.wago.com/209-137</a> |
|--|---|--|

### tools

|  |   |  |
|--|---|--|
|  | <b>Item no.: 209-132</b><br>Operating tool; for connecting comb-style jumper bar; 2-way; of insulating material | <a href="http://www.wago.com/209-132">www.wago.com/209-132</a> |
|--|---|--|

|  |  |  |
|--|--|--|
|  | <b>Item no.: 210-657</b><br>Operating tool with partially insulated shaft; Blade (3.5 x 0.5) mm; short | <a href="http://www.wago.com/210-657">www.wago.com/210-657</a> |
|--|--|--|


|  |  |  |
|--|--|--|
|  | <b>Item no.: 210-658</b><br>Operating tool with partially insulated shaft; Blade (3.5 x 0.5) mm; short; angled | <a href="http://www.wago.com/210-658">www.wago.com/210-658</a> |
|--|--|--|


|  |   |  |
|--|---|--|
|  | <b>Item no.: 210-720</b><br>Operating tool with partially insulated shaft; Type 2, blade (3.5 x 0.5) mm | <a href="http://www.wago.com/210-720">www.wago.com/210-720</a> |
|--|---|--|


### General accessories

|  |   |  |
|--|---|--|
|  | <b>Item no.: 209-123</b><br>Mounting foot with screw; can be screwed on terminal blocks with fixing flange; 6.4 mm wide | <a href="http://www.wago.com/209-123">www.wago.com/209-123</a> |
|--|---|--|

### ferrule


|  |   |  |
|--|---|--|
|  | <b>Item no.: 216-101</b><br>Ferrule; Sleeve for 0.5 mm <sup>2</sup> / AWG 22; uninsulated; electro-tin plated | <a href="http://www.wago.com/216-101">www.wago.com/216-101</a> |
|--|---|--|


|  |  |  |
|--|--|--|
|  | <b>Item no.: 216-102</b><br>Ferrule; Sleeve for 0.75 mm <sup>2</sup> / AWG 20; uninsulated; electro-tin plated | <a href="http://www.wago.com/216-102">www.wago.com/216-102</a> |
|--|--|--|


|  |   |  |
|--|---|--|
|  | <b>Item no.: 216-103</b><br>Ferrule; Sleeve for 1 mm <sup>2</sup> / AWG 18; uninsulated; electro-tin plated | <a href="http://www.wago.com/216-103">www.wago.com/216-103</a> |
|--|---|--|




















|  |   |  |
|--|---|--|
|  | <b>Item no.: 216-104</b><br>Ferrule; Sleeve for 1.5 mm <sup>2</sup> / AWG 16; uninsulated; electro-tin plated | <a href="http://www.wago.com/216-104">www.wago.com/216-104</a> |
|--|---|--|

|  |   |  |
|--|---|--|
|  | <b>Item no.: 216-106</b><br>Ferrule; Sleeve for 2.5 mm <sup>2</sup> / AWG 14; uninsulated; electro-tin plated | <a href="http://www.wago.com/216-106">www.wago.com/216-106</a> |
|--|---|--|

|  |   |  |
|--|---|--|
|  | <b>Item no.: 216-121</b><br>Ferrule; Sleeve for 0.5 mm <sup>2</sup> / AWG 22; uninsulated; electro-tin plated | <a href="http://www.wago.com/216-121">www.wago.com/216-121</a> |
|--|---|--|

|  |  |  |
|--|--|--|
|  | <b>Item no.: 216-122</b><br>Ferrule; Sleeve for 0.75 mm <sup>2</sup> / AWG 20; uninsulated; electro-tin plated | <a href="http://www.wago.com/216-122">www.wago.com/216-122</a> |
|--|--|--|

|  |   |  |
|--|---|--|
|  | <b>Item no.: 216-123</b><br>Ferrule; Sleeve for 1 mm <sup>2</sup> / AWG 18; uninsulated; electro-tin plated | <a href="http://www.wago.com/216-123">www.wago.com/216-123</a> |
|--|---|--|

|  |  |  |
|--|--|--|
|    | <b>Item no.: 216-124</b><br>Ferrule; Sleeve for 1.5 mm <sup>2</sup> / AWG 16; uninsulated; electro-tin plated  | <a href="http://www.wago.com/216-124">www.wago.com/216-124</a> |
|    | <b>Item no.: 216-131</b><br>Ferrule; Sleeve for 0.25 mm <sup>2</sup> / AWG 24; uninsulated; electro-tin plated | <a href="http://www.wago.com/216-131">www.wago.com/216-131</a> |
|    | <b>Item no.: 216-132</b><br>Ferrule; Sleeve for 0.34 mm <sup>2</sup> / AWG 24; uninsulated; electro-tin plated | <a href="http://www.wago.com/216-132">www.wago.com/216-132</a> |
|    | <b>Item no.: 216-151</b><br>Ferrule; Sleeve for 0.25 mm <sup>2</sup> / AWG 24; uninsulated; electro-tin plated | <a href="http://www.wago.com/216-151">www.wago.com/216-151</a> |
|    | <b>Item no.: 216-152</b><br>Ferrule; Sleeve for 0.34 mm <sup>2</sup> / AWG 24; uninsulated; electro-tin plated | <a href="http://www.wago.com/216-152">www.wago.com/216-152</a> |
|    | <b>Item no.: 216-201</b><br>Ferrule; Sleeve for 0.5 mm <sup>2</sup> / AWG 22; insulated; electro-tin plated    | <a href="http://www.wago.com/216-201">www.wago.com/216-201</a> |
|    | <b>Item no.: 216-202</b><br>Ferrule; Sleeve for 0.75 mm <sup>2</sup> / AWG 20; insulated; electro-tin plated   | <a href="http://www.wago.com/216-202">www.wago.com/216-202</a> |
|    | <b>Item no.: 216-203</b><br>Ferrule; Sleeve for 1 mm <sup>2</sup> / AWG 18; insulated; electro-tin plated      | <a href="http://www.wago.com/216-203">www.wago.com/216-203</a> |
|    | <b>Item no.: 216-204</b><br>Ferrule; Sleeve for 1.5 mm <sup>2</sup> / AWG 16; insulated; electro-tin plated    | <a href="http://www.wago.com/216-204">www.wago.com/216-204</a> |
|   | <b>Item no.: 216-205</b><br>Ferrule; Sleeve for 2.08 mm <sup>2</sup> / AWG 14; insulated; electro-tin plated   | <a href="http://www.wago.com/216-205">www.wago.com/216-205</a> |
|  | <b>Item no.: 216-206</b><br>Ferrule; Sleeve for 2.5 mm <sup>2</sup> / AWG 14; insulated; electro-tin plated    | <a href="http://www.wago.com/216-206">www.wago.com/216-206</a> |
|  | <b>Item no.: 216-221</b><br>Ferrule; Sleeve for 0.5 mm <sup>2</sup> / AWG 22; insulated; electro-tin plated    | <a href="http://www.wago.com/216-221">www.wago.com/216-221</a> |
|  | <b>Item no.: 216-222</b><br>Ferrule; Sleeve for 0.75 mm <sup>2</sup> / AWG 20; insulated; electro-tin plated   | <a href="http://www.wago.com/216-222">www.wago.com/216-222</a> |
|  | <b>Item no.: 216-223</b><br>Ferrule; Sleeve for 1 mm <sup>2</sup> / AWG 18; insulated; electro-tin plated      | <a href="http://www.wago.com/216-223">www.wago.com/216-223</a> |
|  | <b>Item no.: 216-224</b><br>Ferrule; Sleeve for 1.5 mm <sup>2</sup> / AWG 16; insulated; electro-tin plated    | <a href="http://www.wago.com/216-224">www.wago.com/216-224</a> |
|  | <b>Item no.: 216-301</b><br>Ferrule; Sleeve for 0.25 mm <sup>2</sup> / AWG 24; insulated; electro-tin plated   | <a href="http://www.wago.com/216-301">www.wago.com/216-301</a> |
|  | <b>Item no.: 216-302</b><br>Ferrule; Sleeve for 0.34 mm <sup>2</sup> / AWG 24; insulated; electro-tin plated   | <a href="http://www.wago.com/216-302">www.wago.com/216-302</a> |
|  | <b>Item no.: 216-321</b><br>Ferrule; Sleeve for 0.25 mm <sup>2</sup> / AWG 24; insulated; electro-tin plated   | <a href="http://www.wago.com/216-321">www.wago.com/216-321</a> |
|  | <b>Item no.: 216-322</b><br>Ferrule; Sleeve for 0.34 mm <sup>2</sup> / AWG 24; insulated; electro-tin plated   | <a href="http://www.wago.com/216-322">www.wago.com/216-322</a> |

#### End plate



**Item no.: 261-361**  
End plate; with fixing flange

[www.wago.com/261-361](http://www.wago.com/261-361)

---

#### Marking accessories



**Item no.: 210-832**  
Marking strips; on reel; 3 mm wide; plain; Self-adhesive

[www.wago.com/210-832](http://www.wago.com/210-832)



**Item no.: 210-833**  
Marking strips; on reel; 6 mm wide; plain; Self-adhesive

[www.wago.com/210-833](http://www.wago.com/210-833)

#### Downloads

##### Documentation

##### Bid Text

---

|                 |              |                |          |
|-----------------|--------------|----------------|----------|
| 261-337/342-000 | Oct 11, 2017 | DOC<br>25.6 kB | Download |
|-----------------|--------------|----------------|----------|

---

#### smartDATA

##### CAD data

---

|                             |     |          |
|-----------------------------|-----|----------|
| 3D Download 261-337/342-000 | URL | Download |
|-----------------------------|-----|----------|

---

Subject to changes.