

Data sheet | Item number: 280-856/281-415

Fuse plug; 5 mm wide; with soldered miniature fuse; with additional indicator lamp; red LED; AC 15 - 30 V; 2 A FF



www.wago.com/280-856/281-415



RoHS Compliant

[BOMcheck.net](https://www.bomcheck.net)

Color: ■

Data

Electrical data

Ratings per IEC/EN 60664-1

Rated voltage (III / 3)	125 V
Rated current	5 A
Legend (ratings)	(III / 3) ≙ Overvoltage category III / Pollution degree 3

Geometrical Data

Width	5 mm / 0.197 inch
Plug width	5 mm / 0.197 inch

Mechanical data

Marking level	without marking level
---------------	-----------------------

Material Data






Color	gray
Insulating material	Polyamide 66 (PA 66)
Fire load	0.068 MJ
Weight	2.94 g

Commercial data

Country of origin	DE
GTIN	4050821864998
Customs Tariff No.	85369010000
Product Group	1 (Rail Mounted Terminal Blocks)

Compatible products

clamps

	Item no.: 280-610 3-conductor carrier terminal block; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm ² ; CAGE CLAMP®	www.wago.com/280-610
	Item no.: 280-616 2-conductor carrier terminal block; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm ² ; CAGE CLAMP®	www.wago.com/280-616
	Item no.: 280-686 4-conductor carrier terminal block; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm ² ; CAGE CLAMP®	www.wago.com/280-686
	Item no.: 280-816 4-conductor carrier terminal block; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm ² ; CAGE CLAMP®	www.wago.com/280-816
	Item no.: 280-916 2-conductor carrier terminal block; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm ² ; CAGE CLAMP®	www.wago.com/280-916

Subject to changes.