


Data sheet | Item number: 289-540

Interface module; with D-subminiature male connector; 9-pole; for mating connectors with IDC; Vertical mounting




www.wago.com/289-540




Similar to picture

RoHS Compliant

BOMcheck.net





Data

Electrical data

Operating voltage	≤ 100 VAC; ≤ 125 VDC
Nominal current	2 A
Contact resistance (max.)	30 mΩ

Safety and protection:

Rated voltage	100 V
Rated impulse voltage	0.8 kV
Pollution degree	2
Degree of protection	IP20

Connection data

No. of poles	9
Connection type (1)	System
No. of poles	9
Pluggable connector	D-subminiature; male connector
For mating connectors	With IDC
Mating direction	Vertical



Pull relief	Stud bolts UNC 4-40
Connection type (2)	Field
No. of poles 2	9
Design 2	PCB terminal blocks, 3-row
Connection technology 2	CAGE CLAMP®
WAGO terminal 2	WAGO 236 Series Series
Solid conductor (2)	0.08 ... 2.5 mm ² / 28 ... 12 AWG
Fine-stranded conductor (2)	0.08 ... 2.5 mm ² / 28 ... 12 AWG
Strip length (2)	5 ... 6 mm / 0.2 ... 0.24 Inch
Note (conductor cross-section)	12 AWG: THHN, THWN
Performance level	2 / 200 mating cycles

Geometrical Data

Width	38 mm / 1.496 inch
Height from upper-edge of DIN-35 rail	34 mm / 1.339 inch
Depth	85 mm / 3.346 inch

Mechanical data

Type of mounting	DIN-35 rail
Housing design	Mounting carrier

Material Data

Contact material (pluggable connector)	Au over Ni
Fire load	0.762 MJ
Weight	47.426 g

Environmental Requirements

Surrounding air (operating) temperature	-20 ... 50 °C
Surrounding air (storage) temperature	-40 ... 70 °C
Relative humidity	≤ 85 % (non condensing)

Standards and specifications

Standards/specifications	UL 840
--------------------------	--------

Commercial data

Country of origin	DE
GTIN	4045454466121
Customs Tariff No.	85369010000
Product Group	6 (Interface Electronics)

Approvals / Certificates

UL-Approvals

Logo	Approval	Certificate name
	UL Underwriters Laboratories Inc. (ORDINARY LOCATIONS)	E175199 Vol.2 Sec.1

Compatible products

tools



Item no.: 210-720

Operating tool with partially insulated shaft; Type 2, blade (3.5 x 0.5) mm

www.wago.com/210-720

Marking accessories



Item no.: 709-177

Marking strips; on reel; 7.5 mm wide; not stretchable; plain; snap-on type

www.wago.com/709-177



Item no.: 709-178

Marking strips; on reel; 7.5 mm wide; not stretchable; plain; snap-on type

www.wago.com/709-178



Item no.: 709-196

Marking strips; for laser printer

www.wago.com/709-196

Downloads

Documentation

Additional Information

Disposal; Electrical and electronic equipment, Packaging	Oct 15, 2018	Download
		265.8 kB

Subject to changes.