

Data sheet | Item number: 722-732/005-000

Female connector for rail-mount terminal blocks; straight; 100% protected against mismatching; Pin spacing 7.5 mm; 2-pole

www.wago.com/722-732/005-000



RoHS 
Compliant

[BOMcheck.net](https://www.bomcheck.net)

Item description

- Pluggable connectors for rail-mounted terminal blocks equipped with CAGE CLAMP®
- Female connectors with long contact pins connect to the termination ports of 280 Series rail-mounted terminal blocks
- Female connectors are touch-proof when unmated, providing a pluggable, live output
- 100% protected against mismatching
- Coding option available

Other versions (or variants) can be requested from WAGO Sales or configured at <https://configurator.wago.com/>. Other pole numbers

Data

Electrical data

Ratings per IEC/EN 60664-1

Legend (ratings)

(III / 2) ≙ Overvoltage category III / Pollution degree 2

Approvals per UL 1059

Rated voltage UL (Use Group B)	300 V
Rated current UL (Use Group B)	15 A
Rated voltage UL (Use Group D)	300 V
Rated current UL (Use Group D)	10 A

Approvals per CSA

Rated voltage CSA (Use Group B)	300 V
Rated current CSA (Use Group B)	15 A
Rated voltage CSA (Use Group D)	300 V
Rated current CSA (Use Group D)	10 A

Connection data

Total number of potentials	3
Number of levels	1

Geometrical Data

Pin spacing	7.5 mm (0.295 inch)
-------------	---------------------

Plug connection

Contact type (pluggable connector)	Female connector/socket
Connector connection type	for front-entry wiring terminal block
Mismating protection	Yes

Material Data

Color	lichtgrau
Material group	I
Insulating material	Polyamide 66 (PA 66)
Flammability class per UL94	V0
Contact material	Electrolytic copper (Ecu)
Contact plating	tin-plated

Environmental Requirements

Limit temperature range	-60 ... +100 °C
-------------------------	-----------------

Commercial data

Country of origin	DE
Customs Tariff No.	85366990990

Product Group

3 (Multi Conn. System)

Compatible products

check



Item no.: 231-662

Test plugs for female connectors; for 7.5 mm and 7.62 mm pin spacing

www.wago.com/231-662

Subject to changes.

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169

Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?

We are always happy to take your call at +49 (571) 887-44222.