

## Data

### Electrical data

#### Ratings per IEC/EN 60664-1

|                                 |   |
|---------------------------------|---|
| Rated voltage (III / 3)         | 250 V   |
| Rated impulse voltage (III / 3) | 4 kV  |
| Rated current                   | 10 A  |
| Legend (ratings)                | (III / 3) ≙ Overvoltage category III / Pollution degree 3 |

### Connection data

|                                   |  |
|-----------------------------------|--|
| Connection technology             | CAGE CLAMP®                                  |
| Actuation type                    | Operating tool                               |
| Connectable conductor materials   | Copper<br>Aluminum                           |
| Solid conductor                   | 0.08 ... 1.5 mm <sup>2</sup> / 28 ... 16 AWG |
| Fine-stranded conductor           | 0.08 ... 1.5 mm <sup>2</sup> / 28 ... 16 AWG |
| Strip length                      | 8 ... 10 mm / 0.31 ... 0.39 Inch             |
| Total number of connection points | 32   |
| Total number of potentials        | 8  |
| Number of levels                  | 8  |
| Type of wiring                    | Front-entry wiring                           |

### Geometrical Data

|       |                    |
|-------|--------------------|
| Width | 7.62 mm / 0.3 inch |
|-------|--------------------|

|                                       |                      |
|---------------------------------------|----------------------|
| Height from upper-edge of DIN-35 rail | 58.5 mm / 2.303 inch |
| Depth                                 | 226 mm / 8.898 inch  |

### Mechanical data

|                  |                |
|------------------|----------------|
| Design           | horizontal     |
| Type of mounting | DIN-35 rail    |
| Marking          | plain          |
| Marking level    | Center marking |

### Material Data

|                     |                      |
|---------------------|----------------------|
| Color               | white                |
| Insulating material | Polyamide 66 (PA 66) |
| Fire load           | 1.187 MJ             |
| Weight              | 73.838 g             |

### Commercial data

|                    |               |
|--------------------|---------------|
| Country of origin  | DE            |
| GTIN               | 4045454188009 |
| Customs Tariff No. | 85369010000   |

### Approvals / Certificates

#### Country specific Approvals



| Logo   | Approval                              | Certificate name |
|--|---------------------------------------|------------------|
|  | CCA<br>DEKRA Certification B.V.       | NTR NL 7485      |
|  | CSA<br>DEKRA Certification B.V.       | 70048845         |
|  | KEMA/KEUR<br>DEKRA Certification B.V. | 2192101.01       |

#### UL-Approvals




| Logo   | Approval                             | Certificate name |
|--|--------------------------------------|------------------|
|  | UR<br>Underwriters Laboratories Inc. | E45172           |

## Compatible products

## tools

|  |   |  |
|--|---|--|
|  | <b>Item no.: 210-647</b><br>Operating tool with partially insulated shaft; Blade (2.5 x 0.4) mm; short  | <a href="http://www.wago.com/210-647">www.wago.com/210-647</a> |
|  | <b>Item no.: 210-719</b><br>Operating tool with partially insulated shaft; Type 1, blade (2.5 x 0.4) mm | <a href="http://www.wago.com/210-719">www.wago.com/210-719</a> |
















## Insulation stop

|  |   |  |
|--|---|--|
|  | <b>Item no.: 727-197</b><br>Insulation stop; 0.08 - 0.2 mm <sup>2</sup> "s" (0.14 mm <sup>2</sup> "f-st"); 8 pieces/strip | <a href="http://www.wago.com/727-197">www.wago.com/727-197</a> |
|  | <b>Item no.: 727-198</b><br>Insulation stop; 0.25 mm <sup>2</sup> "s"; 0.14 - 0.25 mm <sup>2</sup> "f-st"; 8 pieces/strip | <a href="http://www.wago.com/727-198">www.wago.com/727-198</a> |
|  | <b>Item no.: 727-199</b><br>Insulation stop; 0.25 - 0.5 mm <sup>2</sup> "s+f-st"; 8 pieces/strip                          | <a href="http://www.wago.com/727-199">www.wago.com/727-199</a> |

## Marking accessories

|  |   |  |
|--|---|--|
|    | <b>Item no.: 2009-115</b><br>WMB-Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type         | <a href="http://www.wago.com/2009-115">www.wago.com/2009-115</a>                 |
|   | <b>Item no.: 2009-115/000-002</b><br>WMB-Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type | <a href="http://www.wago.com/2009-115/000-002">www.wago.com/2009-115/000-002</a> |
|  | <b>Item no.: 2009-115/000-006</b><br>WMB-Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type | <a href="http://www.wago.com/2009-115/000-006">www.wago.com/2009-115/000-006</a> |
|  | <b>Item no.: 2009-115/000-007</b><br>WMB-Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type | <a href="http://www.wago.com/2009-115/000-007">www.wago.com/2009-115/000-007</a> |
|  | <b>Item no.: 2009-115/000-012</b><br>WMB-Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type | <a href="http://www.wago.com/2009-115/000-012">www.wago.com/2009-115/000-012</a> |
|  | <b>Item no.: 2009-115/000-017</b><br>WMB-Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type | <a href="http://www.wago.com/2009-115/000-017">www.wago.com/2009-115/000-017</a> |
|  | <b>Item no.: 2009-115/000-023</b><br>WMB-Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type | <a href="http://www.wago.com/2009-115/000-023">www.wago.com/2009-115/000-023</a> |
|  | <b>Item no.: 2009-115/000-024</b><br>WMB-Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type | <a href="http://www.wago.com/2009-115/000-024">www.wago.com/2009-115/000-024</a> |
|  | <b>Item no.: 209-128</b><br>Adaptor   | <a href="http://www.wago.com/209-128">www.wago.com/209-128</a>                   |

Item no.: 793-501

|  |   |  |
|--|---|--|
|    | WMB marking card; as card; not stretchable; plain; snap-on type   | <a href="http://www.wago.com/793-501">www.wago.com/793-501</a>                   |
|    | <b>Item no.: 793-501/000-002</b><br>WMB marking card; as card; not stretchable; plain; snap-on type   | <a href="http://www.wago.com/793-501/000-002">www.wago.com/793-501/000-002</a>   |
|    | <b>Item no.: 793-501/000-005</b><br>WMB marking card; as card; not stretchable; plain; snap-on type   | <a href="http://www.wago.com/793-501/000-005">www.wago.com/793-501/000-005</a>   |
|    | <b>Item no.: 793-501/000-006</b><br>WMB marking card; as card; not stretchable; plain; snap-on type   | <a href="http://www.wago.com/793-501/000-006">www.wago.com/793-501/000-006</a>   |
|    | <b>Item no.: 793-501/000-007</b><br>WMB marking card; as card; not stretchable; plain; snap-on type   | <a href="http://www.wago.com/793-501/000-007">www.wago.com/793-501/000-007</a>   |
|    | <b>Item no.: 793-501/000-012</b><br>WMB marking card; as card; not stretchable; plain; snap-on type   | <a href="http://www.wago.com/793-501/000-012">www.wago.com/793-501/000-012</a>   |
|    | <b>Item no.: 793-501/000-017</b><br>WMB marking card; as card; not stretchable; plain; snap-on type   | <a href="http://www.wago.com/793-501/000-017">www.wago.com/793-501/000-017</a>   |
|  | <b>Item no.: 793-501/000-023</b><br>WMB marking card; as card; not stretchable; plain; snap-on type   | <a href="http://www.wago.com/793-501/000-023">www.wago.com/793-501/000-023</a>   |
|  | <b>Item no.: 793-501/000-024</b><br>WMB marking card; as card; not stretchable; plain; snap-on type   | <a href="http://www.wago.com/793-501/000-024">www.wago.com/793-501/000-024</a>   |
|  | <b>Item no.: 793-5501</b><br>WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type         | <a href="http://www.wago.com/793-5501">www.wago.com/793-5501</a>                 |
|  | <b>Item no.: 793-5501/000-002</b><br>WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type | <a href="http://www.wago.com/793-5501/000-002">www.wago.com/793-5501/000-002</a> |
|  | <b>Item no.: 793-5501/000-005</b><br>WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type                                       | <a href="http://www.wago.com/793-5501/000-005">www.wago.com/793-5501/000-005</a> |
|  | <b>Item no.: 793-5501/000-006</b><br>WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type                                       | <a href="http://www.wago.com/793-5501/000-006">www.wago.com/793-5501/000-006</a> |
|  | <b>Item no.: 793-5501/000-007</b><br>WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type                                       | <a href="http://www.wago.com/793-5501/000-007">www.wago.com/793-5501/000-007</a> |
|  | <b>Item no.: 793-5501/000-012</b><br>WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type                                       | <a href="http://www.wago.com/793-5501/000-012">www.wago.com/793-5501/000-012</a> |



**Item no.: 793-5501/000-017**  
WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type

[www.wago.com/793-5501/000-017](http://www.wago.com/793-5501/000-017)



**Item no.: 793-5501/000-023**  
WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type

[www.wago.com/793-5501/000-023](http://www.wago.com/793-5501/000-023)



**Item no.: 793-5501/000-024**  
WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type

[www.wago.com/793-5501/000-024](http://www.wago.com/793-5501/000-024)



**Item no.: 793-933**  
WMB-Multibeschreibungssystem; Aufdruck senkrecht; E0.0, E0.1, ..., E9.6, E9.7 (je 1x); für SPS-Eingangskennzeichnung; für Klemmenbreite 5 - 17,5 mm; 10 Streifen à 10 Schilder pro Karte

[www.wago.com/793-933](http://www.wago.com/793-933)

### Carrier rail



**Item no.: 210-114**  
Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; unslotted; similar to EN 60715

[www.wago.com/210-114](http://www.wago.com/210-114)



**Item no.: 210-118**  
Steel carrier rail; 35 x 15 mm; 2.3 mm thick; 2 m long; unslotted; according to EN 60715

[www.wago.com/210-118](http://www.wago.com/210-118)



**Item no.: 210-197**  
Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; slotted; similar to EN 60715

[www.wago.com/210-197](http://www.wago.com/210-197)



**Item no.: 210-198**  
Copper carrier rail; 35 x 15 mm; 2.3 mm thick; 2 m long; unslotted; according to EN 60715

[www.wago.com/210-198](http://www.wago.com/210-198)



**Item no.: 210-506**  
Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; unslotted; galvanized; similar to EN 60715

[www.wago.com/210-506](http://www.wago.com/210-506)



**Item no.: 210-508**  
Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; slotted; galvanized; similar to EN 60715

[www.wago.com/210-508](http://www.wago.com/210-508)

### General accessories



**Item no.: 249-109**  
Wire harness support

[www.wago.com/249-109](http://www.wago.com/249-109)

### check



**Item no.: 210-137**  
Test plug; 2.3 mm Ø; with 500 mm cable

[www.wago.com/210-137](http://www.wago.com/210-137)



**Item no.: 210-297**  
Step-down test plug; from 4mm socket to 2mm plug

[www.wago.com/210-297](http://www.wago.com/210-297)

### Jumper



**Item no.: 709-107**  
Wire commoning chain; insulated; 32 connections





















[www.wago.com/709-107](http://www.wago.com/709-107)




















### ferrule










**Item no.: 216-101**  
Ferrule; Sleeve for 0.5 mm<sup>2</sup> / AWG 22; uninsulated; electro-tin plated

[www.wago.com/216-101](http://www.wago.com/216-101)

|  |  |  |
|--|--|--|
|    | <b>Item no.: 216-102</b><br>Ferrule; Sleeve for 0.75 mm <sup>2</sup> / AWG 20; uninsulated; electro-tin plated | <a href="http://www.wago.com/216-102">www.wago.com/216-102</a> |
|    | <b>Item no.: 216-103</b><br>Ferrule; Sleeve for 1 mm <sup>2</sup> / AWG 18; uninsulated; electro-tin plated    | <a href="http://www.wago.com/216-103">www.wago.com/216-103</a> |
|    | <b>Item no.: 216-104</b><br>Ferrule; Sleeve for 1.5 mm <sup>2</sup> / AWG 16; uninsulated; electro-tin plated  | <a href="http://www.wago.com/216-104">www.wago.com/216-104</a> |
|    | <b>Item no.: 216-121</b><br>Ferrule; Sleeve for 0.5 mm <sup>2</sup> / AWG 22; uninsulated; electro-tin plated  | <a href="http://www.wago.com/216-121">www.wago.com/216-121</a> |
|    | <b>Item no.: 216-122</b><br>Ferrule; Sleeve for 0.75 mm <sup>2</sup> / AWG 20; uninsulated; electro-tin plated | <a href="http://www.wago.com/216-122">www.wago.com/216-122</a> |
|    | <b>Item no.: 216-123</b><br>Ferrule; Sleeve for 1 mm <sup>2</sup> / AWG 18; uninsulated; electro-tin plated    | <a href="http://www.wago.com/216-123">www.wago.com/216-123</a> |
|    | <b>Item no.: 216-124</b><br>Ferrule; Sleeve for 1.5 mm <sup>2</sup> / AWG 16; uninsulated; electro-tin plated  | <a href="http://www.wago.com/216-124">www.wago.com/216-124</a> |
|    | <b>Item no.: 216-131</b><br>Ferrule; Sleeve for 0.25 mm <sup>2</sup> / AWG 24; uninsulated; electro-tin plated | <a href="http://www.wago.com/216-131">www.wago.com/216-131</a> |
|    | <b>Item no.: 216-132</b><br>Ferrule; Sleeve for 0.34 mm <sup>2</sup> / AWG 24; uninsulated; electro-tin plated | <a href="http://www.wago.com/216-132">www.wago.com/216-132</a> |
|   | <b>Item no.: 216-151</b><br>Ferrule; Sleeve for 0.25 mm <sup>2</sup> / AWG 24; uninsulated; electro-tin plated | <a href="http://www.wago.com/216-151">www.wago.com/216-151</a> |
|  | <b>Item no.: 216-152</b><br>Ferrule; Sleeve for 0.34 mm <sup>2</sup> / AWG 24; uninsulated; electro-tin plated | <a href="http://www.wago.com/216-152">www.wago.com/216-152</a> |
|  | <b>Item no.: 216-201</b><br>Ferrule; Sleeve for 0.5 mm <sup>2</sup> / AWG 22; insulated; electro-tin plated    | <a href="http://www.wago.com/216-201">www.wago.com/216-201</a> |
|  | <b>Item no.: 216-202</b><br>Ferrule; Sleeve for 0.75 mm <sup>2</sup> / AWG 20; insulated; electro-tin plated   | <a href="http://www.wago.com/216-202">www.wago.com/216-202</a> |
|  | <b>Item no.: 216-203</b><br>Ferrule; Sleeve for 1 mm <sup>2</sup> / AWG 18; insulated; electro-tin plated      | <a href="http://www.wago.com/216-203">www.wago.com/216-203</a> |
|  | <b>Item no.: 216-204</b><br>Ferrule; Sleeve for 1.5 mm <sup>2</sup> / AWG 16; insulated; electro-tin plated    | <a href="http://www.wago.com/216-204">www.wago.com/216-204</a> |
|  | <b>Item no.: 216-221</b><br>Ferrule; Sleeve for 0.5 mm <sup>2</sup> / AWG 22; insulated; electro-tin plated    | <a href="http://www.wago.com/216-221">www.wago.com/216-221</a> |
|  | <b>Item no.: 216-222</b><br>Ferrule; Sleeve for 0.75 mm <sup>2</sup> / AWG 20; insulated; electro-tin plated   | <a href="http://www.wago.com/216-222">www.wago.com/216-222</a> |
|  | <b>Item no.: 216-223</b><br>Ferrule; Sleeve for 1 mm <sup>2</sup> / AWG 18; insulated; electro-tin plated      | <a href="http://www.wago.com/216-223">www.wago.com/216-223</a> |
|  | <b>Item no.: 216-224</b><br>Ferrule; Sleeve for 1.5 mm <sup>2</sup> / AWG 16; insulated; electro-tin plated    | <a href="http://www.wago.com/216-224">www.wago.com/216-224</a> |
|  | <b>Item no.: 216-301</b><br>Ferrule; Sleeve for 0.25 mm <sup>2</sup> / AWG 24; insulated; electro-tin plated   | <a href="http://www.wago.com/216-301">www.wago.com/216-301</a> |

|  |  |  |
|--|--|--|
|     | <p><b>Item no.: 216-302</b><br/>                     Ferrule; Sleeve for 0.34 mm<sup>2</sup> / AWG 24; insulated; electro-tin plated</p> | <a href="http://www.wago.com/216-302">www.wago.com/216-302</a> |
|     | <p><b>Item no.: 216-321</b><br/>                     Ferrule; Sleeve for 0.25 mm<sup>2</sup> / AWG 24; insulated; electro-tin plated</p> | <a href="http://www.wago.com/216-321">www.wago.com/216-321</a> |
|     | <p><b>Item no.: 216-322</b><br/>                     Ferrule; Sleeve for 0.34 mm<sup>2</sup> / AWG 24; insulated; electro-tin plated</p> | <a href="http://www.wago.com/216-322">www.wago.com/216-322</a> |
| <b>End plate</b>   |  |  |
|    | <p><b>Item no.: 727-105</b><br/>                     8-level end plate; marking: 0-1-2-3-4-5-6-7--7-6-5-4-3-2-1; 7.62 mm thick</p>       | <a href="http://www.wago.com/727-105">www.wago.com/727-105</a> |
|    | <p><b>Item no.: 727-106</b><br/>                     8-level end plate; marking: a-b-c-d-e-f-g-h--h-g-f-e-d-c-b-a; 7.62 mm thick</p>     | <a href="http://www.wago.com/727-106">www.wago.com/727-106</a> |
|    | <p><b>Item no.: 727-107</b><br/>                     8-level end plate; marking: 7-6-5-4-3-2-1-0--0-1-2-3-4-5-6-7; 7.62 mm thick</p>     | <a href="http://www.wago.com/727-107">www.wago.com/727-107</a> |
|    | <p><b>Item no.: 727-108</b><br/>                     8-level end plate; marking: h-g-f-e-d-c-b-a--a-b-c-d-e-f-g-h; 7.62 mm thick</p>     | <a href="http://www.wago.com/727-108">www.wago.com/727-108</a> |
|    | <p><b>Item no.: 727-113</b><br/>                     8-level end plate; plain; 7.62 mm thick</p>   | <a href="http://www.wago.com/727-113">www.wago.com/727-113</a> |
|   | <p><b>Item no.: 727-114</b><br/>                     8-level end plate; plain; 7.62 mm thick</p>   | <a href="http://www.wago.com/727-114">www.wago.com/727-114</a> |
|  | <p><b>Item no.: 727-115</b><br/>                     8-level end plate; plain; 7.62 mm thick</p>   | <a href="http://www.wago.com/727-115">www.wago.com/727-115</a> |
|  | <p><b>Item no.: 727-116</b><br/>                     8-level end plate; plain; 7.62 mm thick</p>   | <a href="http://www.wago.com/727-116">www.wago.com/727-116</a> |
|  | <p><b>Item no.: 727-117</b><br/>                     8-level end plate; plain; 7.62 mm thick</p>   | <a href="http://www.wago.com/727-117">www.wago.com/727-117</a> |
|  | <p><b>Item no.: 727-155</b><br/>                     8-level end plate; marking: 0-1-2-3-4-5-6-7--7-6-5-4-3-2-1; 7.62 mm thick</p>       | <a href="http://www.wago.com/727-155">www.wago.com/727-155</a> |
|  | <p><b>Item no.: 727-156</b><br/>                     8-level end plate; marking: a-b-c-d-e-f-g-h--h-g-f-e-d-c-b-a; 7.62 mm thick</p>     | <a href="http://www.wago.com/727-156">www.wago.com/727-156</a> |
|  | <p><b>Item no.: 727-157</b><br/>                     8-level end plate; marking: 7-6-5-4-3-2-1-0--0-1-2-3-4-5-6-7; 7.62 mm thick</p>     | <a href="http://www.wago.com/727-157">www.wago.com/727-157</a> |
|  | <p><b>Item no.: 727-158</b><br/>                     8-level end plate; marking: h-g-f-e-d-c-b-a--a-b-c-d-e-f-g-h; 7.62 mm thick</p>     | <a href="http://www.wago.com/727-158">www.wago.com/727-158</a> |
|  | <p><b>Item no.: 727-159</b><br/>                     8-level end plate; marking: 0-1-2-3-4-5-6-7--7-6-5-4-3-2-1; 7.62 mm thick</p>       | <a href="http://www.wago.com/727-159">www.wago.com/727-159</a> |
|  | <p><b>Item no.: 727-160</b><br/>                     8-level end plate; marking: a-b-c-d-e-f-g-h--h-g-f-e-d-c-b-a; 7.62 mm thick</p>     | <a href="http://www.wago.com/727-160">www.wago.com/727-160</a> |
|  | <p><b>Item no.: 727-161</b><br/>                     8-level end plate; marking: 7-6-5-4-3-2-1-0--0-1-2-3-4-5-6-7; 7.62 mm thick</p>     | <a href="http://www.wago.com/727-161">www.wago.com/727-161</a> |

|  |   |  |
|--|---|--|
|  | <b>Item no.: 727-162</b><br>8-level end plate; marking: h-g-f-e-d-c-b-a--a-b-c-d-e-f-g-h; 7.62 mm thick | <a href="http://www.wago.com/727-162">www.wago.com/727-162</a> |
|  | <b>Item no.: 727-163</b><br>8-level end plate; marking: 0-1-2-3-4-5-6-7--7-6-5-4-3-2-1; 7.62 mm thick   | <a href="http://www.wago.com/727-163">www.wago.com/727-163</a> |
|  | <b>Item no.: 727-164</b><br>8-level end plate; marking: a-b-c-d-e-f-g-h--h-g-f-e-d-c-b-a; 7.62 mm thick | <a href="http://www.wago.com/727-164">www.wago.com/727-164</a> |
|  | <b>Item no.: 727-165</b><br>8-level end plate; marking: 7-6-5-4-3-2-1-0--0-1-2-3-4-5-6-7; 7.62 mm thick | <a href="http://www.wago.com/727-165">www.wago.com/727-165</a> |
|  | <b>Item no.: 727-166</b><br>8-level end plate; marking: h-g-f-e-d-c-b-a--a-b-c-d-e-f-g-h; 7.62 mm thick | <a href="http://www.wago.com/727-166">www.wago.com/727-166</a> |
|  | <b>Item no.: 727-167</b><br>8-level end plate; marking: 0-1-2-3-4-5-6-7--7-6-5-4-3-2-1; 7.62 mm thick   | <a href="http://www.wago.com/727-167">www.wago.com/727-167</a> |
|  | <b>Item no.: 727-168</b><br>8-level end plate; marking: a-b-c-d-e-f-g-h--h-g-f-e-d-c-b-a; 7.62 mm thick | <a href="http://www.wago.com/727-168">www.wago.com/727-168</a> |
|  | <b>Item no.: 727-169</b><br>8-level end plate; marking: 7-6-5-4-3-2-1-0--0-1-2-3-4-5-6-7; 7.62 mm thick | <a href="http://www.wago.com/727-169">www.wago.com/727-169</a> |
|  | <b>Item no.: 727-170</b><br>8-level end plate; marking: h-g-f-e-d-c-b-a--a-b-c-d-e-f-g-h; 7.62 mm thick | <a href="http://www.wago.com/727-170">www.wago.com/727-170</a> |

Downloads

Documentation

Bid Text

|         |              |                |          |
|---------|--------------|----------------|----------|
| 727-132 | Oct 18, 2017 | DOC<br>25.6 kB | Download |
|---------|--------------|----------------|----------|

smartDATA

CAD data

|                     |     |          |
|---------------------|-----|----------|
| 3D Download 727-132 | URL | Download |
|---------------------|-----|----------|

Subject to changes.

WAGO Kontakttechnik GmbH & Co. KG  
 Hansastr. 27  
 32423 Minden  
 Phone: +49571 887-0 | Fax: +49571 887-169  
 Email: [info.de@wago.com](mailto:info.de@wago.com) | Web: [www.wago.com](http://www.wago.com)

Do you have any questions about our products?  
 We are always happy to take your call at +49 (571) 887-44222.