



RoHS   
Compliant

BOMcheck.net

Color:

## Data

### Electrical data

### Ratings per IEC/EN 60664-1

Legend (ratings)

(III / 3) ≙ Overvoltage category III / Pollution degree 3

### Connection data

Actuation type

Operating tool

### Mechanical data

Degree of protection

IP20

### Material Data

Color

white

Insulating material

Polyamide 66 (PA 66)

Flammability class per UL94

V0

Fire load	0.013 MJ
Weight	0.4 g

### Environmental Requirements


Surrounding air (operating) temperature	-35 ... 85 °C
---	---------------

### Commercial data

Country of origin	DE
GTIN	4017332755245
Customs Tariff No.	39269097900
Product Group	20 (WINSTA)

### Approvals / Certificates

#### Country specific Approvals

Logo	Approval	Certificate name
	VDE VDE Prüf- und Zertifizierungsinstitut	40029808

### Downloads

#### Documentation

##### Bid Text

770-131	Jan 29, 2016	DOC	Download
WINSTA Zubehoer		22.0 kB	

### smartDATA

#### CAD data

3D Download 770-131	URL	Download
---------------------	-----	----------

Subject to changes.