



## Data

### Connection data

No. of poles	4
Connectable sheathed cable diameter	6.5 ... 10.5 mm
Abmantellänge	45 mm

### Geometrical Data

Width	23.2 mm / 0.913 inch
Height	16 mm / 0.63 inch
Depth	55 mm / 2.165 inch

### Mechanical data

Degree of protection	IP20
----------------------	------

### Material Data

Insulating material	Polyamide 66 (PA 66)
Flammability class per UL94	V0
Fire load	0.173 MJ



Weight	5.74 g
--------	--------

---

### Environmental Requirements

Surrounding air (operating) temperature	-35 ... 85 °C
---	---------------

---

### Commercial data

Country of origin	DE
GTIN	4045454233372
Customs Tariff No.	85366990990
Product Group	20 (WINSTA)

---

### Downloads

#### Documentation

##### Bid Text

890-514	Mar 15, 2016	DOC	Download
WINSTA MINI 4-polig		24.1 kB	

---

### smartDATA

#### CAD data

3D Download 890-514	URL	Download
---------------------	-----	----------

---

Subject to changes.