



RoHS  Compliant

[BOMcheck.net](https://www.bomcheck.net)

Color:

## Data

### Electrical data

#### Ratings per IEC/EN 60664-1

Legend (ratings)

(III / 3) ≙ Overvoltage category III / Pollution degree 3

### Connection data

No. of poles

2

### Mechanical data

Mounting type

Snap-in

### Material Data

Color

black

Insulating material

Polyamide 66 (PA 66)

Flammability class per UL94

V0



Fire load	0.036 MJ
Weight	1.21 g

### Environmental Requirements

Surrounding air (operating) temperature	-35 ... 85 °C
-----------------------------------------	---------------

### Commercial data

Country of origin	DE
GTIN	4045454526474
Customs Tariff No.	39269097900
Product Group	20 (WINSTA)

### Downloads

#### Documentation

#### Bid Text

890-642	Jan 29, 2016	DOC	Download
WINSTA Accessories		22.0 kB	

### smartDATA

#### CAD data

3D Download 890-642	URL	Download
---------------------	-----	----------

Subject to changes.