

Repair Stick Copper



**extremely fast cure
copper-filled
NSF approval, can be used in drinking water areas**

The WEICON Repair Stick Copper is suited for the very quick repair (processing time: 3 min.) of cracks and leaks even on damp and wet surfaces such as pipes, pipe bends, fittings, flanges, copper gutters, sheets, water heaters, water tanks, hot, cold water lines, freezer and air conditioning systems.

The WEICON Repair Stick Copper can be used in tank construction and apparatus engineering, in the foods, cosmetic and pharmaceutical industries and in many other applications.



Technical Data

Composition	Epoxy resin copper-filled
Composition	pasty
Colour after curing	copper
Mixing ratio by volume resin/hardener	1:1
Density of the mixture	1,9 g/cm ³
Gap bridging max.	15 mm
Processing temperatur	+10 to +30 °C
Curing temperature	+6 to +40 °C
Polt life for 25gr preparation and +20°C (+68°F)	3 min.
Handling strength (35%) after	10 min.
Mechanical loads (50% strength) after	60 min.

The specifications and recommendations given in this technical data sheet must not be seen as guaranteed product characteristics. They are based on our laboratory tests and on practical experience. Since individual application conditions are beyond our knowledge, control and responsibility, this information is provided without any obligation. We do guarantee the continuously high quality of our products. However, own adequate laboratory and practical tests to find out if the product in question meets the requested properties are recommended. A claim cannot be derived from them. The user bears the only responsibility for non-appropriate or other than specified applications.

Final strength (100%) after	24 h
Pressure (DIN 53281-83)	80 N/mm ²
Medium shear strength after 7 days at +20°C (+65°F) DIN 532832 at	Copper sandblasted: 4,8 N/mm ²
Shore hardness D	80
Thermal conductivity (ASTM D 257)	0,7 W/m.K
Linear shrinkage	<1 %
Electrical resistance (ASTM D 149)	5•10 ¹¹ Ohm/cm
Dielectric strength (ASTM D 149)	3,0 kV/mm
Thermal expansion coefficient (ISO 11359)	30-40 x 10 ⁻⁶ K ⁻¹
Temperature resistance	-50 to +120 briefly +150 °C
ISSA-Code	75.530.04/05
IMPA-Code	81 29 75/76

Surface pre-treatment

To ensure a perfect bond, the surfaces to be joined must be clean and dry (e.g., clean and degrease using WEICON Surface Cleaner).

Processing

WEICON Repair Sticks cover gaps of max. 15 mm per procedure. The pot life given is for a material quantity of 25 g at room temperature. If larger quantities are used, the curing time will be faster due to the typical reaction heat of epoxy resins (exothermic reaction). Similarly, higher ambient temperatures shorten the cure time (as a rule of thumb, every +10°C increase above room temperature will halve working and curing time). Temperatures below +16°C will extend working and curing times considerably, while below about +5°C, no reaction will take place at all.

Storage

When kept at a constant room temperature of about +20°C and unopened in dry conditions, WEICON Repair Sticks will keep for at least 18 months. Avoid direct sunlight.

Safety and health

When using WEICON products, the physical, safety technical, toxicological and ecological data and regulations in our EC safety data sheets (www.weicon.com) must be observed.

Available sizes:

10530057	Repair Stick Copper 57 g
10530115	Repair Stick Copper 115 g

Accessories:

11202400	Sealant and Adhesive Remover, 400 ml
11207400	Surface Cleaner, 400 ml
11850200	Hand Protective Foam, 200 ml

WEICON GmbH & Co. KG
(Headquarters)
Germany
phone +49 (0) 251 9322 0
info@weicon.de

WEICON Middle East L.L.C.
United Arab Emirates
phone +971 4 880 25 05
info@weicon.ae

WEICON Inc.
Canada
phone +1 877 620 8889
info@weicon.ca
www.weicon.ca

WEICON Kimya Sanayi Tic. Ltd. Şti.
Turkey
phone +90 (0) 212 465 33 65
info@weicon.com.tr
www.weicon.com.tr

WEICON Romania SRL
Romania
phone +40 (0) 3 65 730 763
office@weicon.com

WEICON SA (Pty) Ltd
South Africa
phone +27 (0) 21 709 0088
info@weicon.co.za

WEICON South East Asia Pte Ltd
Singapore
phone (+65) 6710 7671
info@weicon.com.sg

WEICON Czech Republic s.r.o.
Czech Republic
phone +42 (0) 417 533 013
info@weiconcz.cz

WEICON Ibérica S.L.
Spain
phone +34 (0) 914 7997 34
info@weicon.es