

Workshop-Cleaner



free of solvents and phosphate
bio-degradable

Workshop Cleaner cleans and degreases all metals, plastics, types of rubber, glass, ceramics and wood. It removes grease, oil, resin, rust, wax, nicotine, insect dirt, bitumen and tar specks.

Workshop Cleaner is free of solvent, emulsifier and phosphate compatible with oil separators (ÖNORM B 5105) and, in accordance with EC-guidelines, bio-degradable. It is highly concentrated and can be diluted to the proportion 1:40 (max.).

Workshop Cleaner contains selected foamless tensides and, in addition to manual cleaning, can be used in highpressure cleaners, part washing machines and spray apparatuses (e.g. Pump Dispenser WPS 1500). Special ingredients provide temporary corrosion protection.

ISSA: 53.402.35

Technical data

Colour	blue
Odour	almost odourless
Temperature resistance	+5 bis +90 °C
Shelf life min.	24 months
Special features	solvent-free, biodegradable
Suitable for use with	WPS 1500

Processing

Apply Workshop Cleaner generously to the parts that need to be cleaned, allow it to soak in and wipe it off with a clean cloth. Repeat this action in the event of stubborn stains. The cleaning process can be shortened by warming up the product (max. +90 °C). Particularly coarse dirt can be removed more simply in this way. Do not apply it undiluted to aluminium or zinc coatings (alkaline, concentrated pH value approx. 12). Protect against frost.

Storage

Keep in closed original container. Protect from direct solar radiation. Storage temperature may not exceed +50 °C. Store container at cool and aired place. Store in a dry place.

Note

Any product specifications and recommendations given herein must not be seen as guaranteed product characteristics. They are based on our laboratory tests and on practical experience. Since individual application conditions are beyond our knowledge, control and responsibility, this information is provided without any obligation. We do warrant the continuously high quality of our products being free from defects in accordance with and subject to our General Sales Conditions. However, own adequate laboratory and practical tests to find out if the product in question meets the requested properties are recommended. A claim cannot be derived from them. The user bears the only responsibility for non-appropriate or other than specified applications.

Health and Safety

When using WEICON products, the physical, safety technical, toxicological and ecological data and regulations in our EC safety data sheets (www.weicon.com) must be observed.

WEICON GmbH & Co. KG (Headquarter)

Königsberger Str. 255 · DE-48157 Münster
P.O. Box 84 60 · DE-48045 Münster
Germany

Tel. +49 (0) 251 / 93 22-0
Fax +49 (0) 251 / 93 22-244
Fax +49 (0) 251 / 93 22-233 Export
www.weicon.de · info@weicon.de

WEICON Middle East L.L.C.

Jebel Ali Ind Area 3 · P.O. Box 118 216
Dubai · U.A.E

Phone +971 4 880 25 05
Fax +971 4 880 25 09
Mobile +971 50 545 99 83
www.weicon.ae · info@weicon.ae

WEICON Inc.

20 Steckle Place · Unit 20
Kitchener · Ontario · N2E 2C3
Canada

Phone +1 519 896 5252
Fax +1 519 896 5254
Cell +1 519 590 5168
www.weicon.ca · info@weicon.ca

WEICON Kimya Sanayi Tic. Ltd. Şti.

Yenibosna Mahallesi Yalçın Koreş Caddesi
Arifağa Sokak No: 29 Kat: 3
34530 Yenibosna – İstanbul Turkey
www.weicon.biz.tr · info@weicon.biz.tr

WEICON Romania SRL

Str. Podului Nr.1
547176 Budiu Mic (Targu Mures)
www.weicon.com · office@weicon.com