

# AL-T



high temperature grease  
long-term lubrication

WEICON AL-T high performance grease is a universally usable high temperature grease for long-term lubrication. WEICON AL-T is suitable for rolling and sliding bearings, joints, levers, sliding guides, spindles, spline shafts and at all sliding speeds permitted for grease lubrication.

## Technical data

Abbreviation (DIN 51502)	KPL 2 R -20
Consistency assignment (DIN 51818)	NLGI-class 2
Base	Aluminium complex soap / mineral oil
Colour	dark-brown
VKA-Test (DIN 51 350) welding load	2400 N
VKA-Test (DIN 51 350) goods load	2200 N
VKA-Test (DIN 51350) Spherical cap value (1 Min / 10	2,0 mm
Speed identifying value	400 000
Worked penetration (DIN ISO 2137)	265-295 1/10 mm
Water resistance (DIN 51807)	0 - 90
Temperature resistance	-25 bis +190 °C
Drop point (IP 396)	>210 °C
Kinematic viscosity (DIN 51 562) +40 °C	ca. 230 mm <sup>2</sup> /s
Kinematische Viskosität (DIN 51 562) +100 °C	ca. 16 mm <sup>2</sup> /s
EMCOR-corrosion test (DIN 51 802)	0 / 0
Density at +20 °C (DIN 51757)	0,94 g/cm <sup>3</sup>
Shelf life at least	24 months

## Pretreatment of the surface

Clean surfaces.

## Processing

Apply AL-T evenly.

## Storage

Keep in closed original container. Do not store together with oxidizing agents. Keep container tightly closed and store at cool and aired place. Recommended storage temperature: room temperature.

## Note

Any product specifications and recommendations given herein must not be seen as guaranteed product characteristics. They are based on our laboratory tests and on practical experience. Since individual application conditions are beyond our knowledge, control and

responsibility, this information is provided without any obligation. We do warrant the continuously high quality of our products being free from defects in accordance with and subject to our General Sales Conditions. However, own adequate laboratory and practical tests to find out if the product in question meets the requested properties are recommended. A claim cannot be derived from them. The user bears the only responsibility for non-appropriate or other than specified applications.

## Health and Safety

When using WEICON products, the physical, safety technical, toxicological and ecological data and regulations in our EC safety data sheets ([www.weicon.com](http://www.weicon.com)) must be observed.

### WEICON GmbH & Co. KG (Headquarter)

Königsberger Str. 255 · DE-48157 Münster  
P.O. Box 84 60 · DE-48045 Münster  
Germany

Tel. +49 (0) 251 / 93 22-0  
Fax +49 (0) 251 / 93 22-244  
Fax +49 (0) 251 / 93 22-233 Export  
[www.weicon.de](http://www.weicon.de) · [info@weicon.de](mailto:info@weicon.de)

### WEICON Middle East L.L.C.

Jebel Ali Ind Area 3 · P.O. Box 118 216  
Dubai · U.A.E

Phone +971 4 880 25 05  
Fax +971 4 880 25 09  
Mobile +971 50 545 99 83  
[www.weicon.ae](http://www.weicon.ae) · [info@weicon.ae](mailto:info@weicon.ae)

### WEICON Inc.

20 Steckle Place · Unit 20  
Kitchener · Ontario · N2E 2C3  
Canada

Phone +1 519 896 5252  
Fax +1 519 896 5254  
Cell +1 519 590 5168  
[www.weicon.ca](http://www.weicon.ca) · [info@weicon.ca](mailto:info@weicon.ca)

### WEICON Kimya Sanayi Tic. Ltd. Şti.

Yenibosna Mahallesi Yalçın Koreş Caddesi  
Arifağa Sokak No: 29 Kat: 3  
34530 Yenibosna – İstanbul Turkey  
[www.weicon.biz.tr](http://www.weicon.biz.tr) · [info@weicon.biz.tr](mailto:info@weicon.biz.tr)

### WEICON Romania SRL

Str. Podului Nr.1  
547176 Budiu Mic (Targu Mures)  
[www.weicon.com](http://www.weicon.com) · [office@weicon.com](mailto:office@weicon.com)