TECHNICAL SPECIFICATIONS

Materials:


Unshielded Hood: UL-recognised plastic material

Operating Temperature: -30°C to +110°C

Colour: Black (Standard)
Other colour on request


Shielded Hood: UL-recognised plastic material


Plating: Nickel over Copper
Operating Temperature: -30°C to +90°C
Thumbscrews: UNC 4-40 (Standard)



Features:

- Available in sizes 9 and 25 (15 on request)
- Available in EMI-shielded and unshielded version
- Delivered complete with wires and Sub-D
- Pre-wired connectors on request





Size MHDA	Dim A	Dim B	Dim C
9-way	33,0	15,0	49,5
15-way	41,3	15,0	39,0
25-way	55,1	15,0	39,0

Ordering information:	Unshielded Version
-----------------------	--------------------

Size:	P/N - Kitted:	Product Code:
9-way	2112-0100-01	MHDA09-SMJ6-K-RC
25-way	2112-0100-03	MHDA25-SMJ6-K-RC
9-way	2112-0100-11	MHDA09-PMJ6-K-RC
25-way	2112-0100-13	MHDA25-PMJ6-K-RC
9-way	2112-0101-01	MHDA09-SMJ8-K-RC
25-way	2112-0101-03	MHDA25-SMJ8-K-RC
9-way	2112-0101-11	MHDA09-PMJ8-K-RC
25-way	2112-0101-13	MHDA25-PMJ8-K-RC

Ordering information:

Shielded Version

Size:	P/N - Kitted:	Product Code:
9-way	2112-0105-01	MHDA09-SMJ8-M-K-RC
25-way	2112-0105-03	MHDA25-SMJ8-M-K-RC
9-way	2112-0105-11	MHDA09-PMJ8-M-K-RC
25-way	2112-0105-13	MHDA25-PMJ8-M-K-RC

SMJ6 = Sub-D Female to RJ11 PMJ6 = Sub-D Male to RJ11

SMJ8 = Sub-D Female to RJ45

PMJ8 = Sub-D Male to RJ45

