



NKCR.E191693 Auxiliary Devices

[Page Bottom](#)

Auxiliary Devices

[See General Information for Auxiliary Devices](#)

ABB FRANCE

E191693

ACTIVITE PROTECTION ET CONTROL
3 RUE JEAN PERRIN
CS90009
69687 CHASSIEU CEDEX, FRANCE

Foot operated limit switches, Model Nos. PD or PS followed by 1111 thru 1354.

Limit switches, Models LS30P52-9016, LS30P99-9004, LS30P99-9005, LS30P99-9012, LS30P99-9018, LS31P99-9014, LS39P31-9008, LS35P99-9009, LS35P99-9010, LS39P99-9001, LS39P99-9006, LS39P99-9007, LS40M99-9002, LS40M99-9003, LS40M99-9007, LS45M99-9007, LS60M99-9002;

LS3 f/b 0, 1, 2, 3, 5 f/b P, f/b 0, 1, 3, 4, 5, 6, 7, 9, f/b 0, 1, 2, 3, 4, 5, 6, 7, 8, 9, f/b L, D, C or B, f/b 0, 1, 2, f/b 0, 1, 2, may be f/b -R, -A; LS3 f/b 0, 1, 2, 3, 5 f/b M, f/b 0, 1, 3, 4, 5, 6, 7, 9 f/b 0, 1, 2, 3, 4, 5, 6, 7, 8, 9 f/b L, D, C or B, f/b 0, 1, 2 f/b 0, 1, 2 may be f/b -R, -A; LS4 f/b 0, 3, 5 f/b M, f/b 0, 1, 2, 3, 4, 5, 6, 7, 9 f/b 0, 1, 2, 3, 4, 5, 6, 7, 9, f/b L, D, C or B f/b 0, 1, 2, 3 f/b 0, 1, 2, 3 may be f/b -A; LS4 f/b 0, 3, 5 f/b M, f/b 0, 1, 2, 3, 4, 5, 6, 7, 9 f/b 0, 1, 2, 3, 4, 5, 6, 7, 9 f/b L, D, C or B, f/b 0, 1, 2, 3 f/b 0, 1, 2, 3 may be f/b -A; LS6 f/b 0, 3, 5 f/b M, f/b 0, 1, 2, 3, 4, 5, 6, 7, 9 f/b 0, 1, 2, 3, 4, 5, 6, 7, 9 f/b L, D, C or B f/b 0, 1, 2, 3 f/b 0, 1, 2, 3 may be f/b -A; LS7 f/b 0, 1, 2, 3, 5 f/b P, f/b 0, 1, 3, 4, 5, 6, 7, 9 f/b 0, 1, 2, 3, 4, 5, 6, 7, 8, 9 f/b L, D, C or B, f/b 0, 1, 2 f/b 0, 1, 2 may be f/b -R, -A; LS7 f/b 0, 1, 2, 3, 5 f/b M, f/b 0, 1, 3, 4, 5, 6, 7, 9 f/b 0, 1, 2, 3, 4, 5, 6, 7, 8, 9 f/b L, D, C or B f/b 0, 1, 2 f/b 0, 1, 2 may be f/b -R, -A.

"Red-Top" limit switches, LS3 f/b 0, 1, 2, 3, 4, 5 f/b P, f/b 1, 2, 6, 7, 8, 9 f/b 0, 1, 2, 3, 4, 5, 6, 7, 8, 9, f/b L, D, C or B, f/b 0, 1 f/b 1, 2, f/b -S; LS3 f/b 0, 1, 2, 3, 5 f/b M, f/b 1, 6, 7, 8, 9 f/b 0, 1, 2, 3, 4, 5, 6, 7, 8, 9, f/b L, D, C or B, f/b 0, 1, f/b 1, 2, f/b -S; LS7 f/b 0, 1, 2, 3, 5 f/b P, f/b 1, 2, 6, 7, 8, 9 f/b 0, 1, 2, 3, 4, 5, 6, 7, 8, 9, f/b L, D, C or B f/b 0, 1 f/b 1, 2 f/b -S, -SC, -SCR; LS7 f/b 0, 1, 2, 3, 5 f/b M, f/b 1, 2, 6, 7, 8, 9 f/b 0, 1, 2, 3, 4, 5, 6, 7, 8, 9 f/b L, D, C or B f/b 0, 1, f/b 1, 2, f/b -S, -SC, -SCR; LS4 f/b 0, 3, 5 f/b P, f/b 8 f/b 0 f/b L, D, C or B f/b 0, 1, 2 f/b 0, 1, 2, 3 f/b -S; LS4 f/b 0, 3, 5 f/b P, f/b 8, 9 f/b 0, 8 f/b L, D, C or B f/b 0, 1, 2 f/b 1, 2, 3 f/b -S, -SC, -SCR; LS6 f/b 0, 3, 5 f/b M, f/b 8, 9 f/b 0, 8 f/b L, D, C or B, f/b 0, 1, 2 f/b 0, 1, 2, 3 f/b -S, -SC, -SCrr.

Auxiliary devices LS2 f/b 0, 1, 5, 6 f/b P, M f/b 1, 2, 3, 4, 5, 6, 7, 8, 9 f/b 1, 2, 3, 4, 5, 6, 8 f/b B11, D11 f/b -U f/b 0102, 03, 04, 05, 06, 07, 08, 09, 10.

LS31P41-9001-R, LS31P99-9025, LS33P99-9026, LS72M99-9004, LS73M99-9001-A, LS75M99-9001-R, LS79M98-9003-A.

LS45M99-9001-SCR, LS79M11-9007, LS72M99-9005, LS45M99-9012, LS30P80-9001-S.

Foot operated limit switches, IP, f/b S or D, may be f/b G, R, Y or Z, f/b 1, 2, 3, f/b A, D, B, L, C f/b 0, 1, 2, f/b 0, 1, 2 may be f/b A, D, B, L, C may be f/b 0, 1, 2, may be f/b 0, 1, 2.

[Last Updated](#) on 2012-10-17

[Questions?](#)

[Print this page](#)

[Terms of Use](#)

[Page Top](#)

© 2013 UL LLC

When the UL Leaf Mark is on the product, or when the word "Environment" is included in the UL Mark, please search the [UL Environment database](#) for additional information regarding this product's certification.

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2013 UL LLC".