


RECOMMENDED MOUNTING:

M4 FASTENER WITH 6.00 IN-LB [7.00 XGF-CM] OF TORQUE MAX.



TERMINAL CALL-OUTS MAY ALSO BE LISTED NUMERICALLY

3 - M4 X 4.9 mm
TERMINAL SCREW AND
INTERNAL TOOTHED
LOCK WASHER

CHARACTERISTICS

ELECTRICAL RATING	15A 250VAC UL APPROVED 15A 250VAC VDE APPROVED
TERMINAL	SCREW
OPER. FORCE MAX.	160 GMS
RELEASE FORCE MIN.	42 GMS
PRETRAVEL MAX.	.106 [2.7 mm]
OVERTRAVEL MIN.	.094 [2.4 mm]
MOVE. DIFF. MAX.	.019 [0.5 mm]
REST POSITION MAX.	1.280 [32.5 mm]
OPERATING POSITION	1.173 TO 1.205 [29.8 TO 30.6 mm]

DWN: J. DOLNIK
APVD: SB
DATE: 25-May-04

THIRD ANGLE PROJECTION

THE CONFIDENTIAL AND PROPRIETARY
INFORMATION CONTAINED IN THIS DOCUMENT
IS OWNED BY CHERRY ELECTRICAL PRODUCTS,
A DIVISION OF THE CHERRY CORPORATION WHO
MUST GIVE WRITTEN PERMISSION BEFORE THE
DOCUMENT OR INFORMATION CAN BE COPIED,
DISCLOSED OR USED IN ANY WAY.

TOLERANCE UNLESS SPECIFIED
X XX ± .02 ± 0.015 ± 5.0 ANGLES

CHERRY
ELECTRICAL PRODUCTS

11200 80TH AVENUE
PLEASANT PRAIRIE, WI 53156

SCALE: 2:1

SPEC DRAWING

C ITEM NO. GPTRM01

C 13038 01-Jul-05 JED SG
REV FCN NO DATE PRP APVD

PROJECT 7134

SCALE: 2:1 CH 1 OF 1

ORIGINAL ON PROVE