


Cable Clamps


Cable Clamps - Diamond Shape



Material: Polyamide (Light Gray)
The photo is of HFCN8.


RoHS10

HFCN5 PACK (50 pcs./pkg.)




Attachable by hand.

HFCN6 PACK (50 pcs./pkg.)



HFCN8 PACK (50 pcs./pkg.)



Part Number		Extrusion (Series)	Unit Price 1 ~ 2 pkg(s).	Volume Discount Rate 3~30
Type	No.			
HFCN	5PACK	HFS5		
	6PACK	HFS6		
	8PACK	HFS8 HFS8-45		

50 pcs. per pkg.




Alterations

Part Number - (SET)
HFCN6PACK - SET

Alteration	Code
Set of 300 pcs.	SET

When ordering, please note the quantity. 300 pcs. will be delivered for an order of one HFCN5PACK-SET.


Cable Clamps - Circular



Material: Polyamide (Light Gray)
The photo is of HFCC8.


RoHS10

HFCC5 PACK (50 pcs./pkg.)




Attachable by hand.

HFCC6 PACK (50 pcs./pkg.)



HFCC8 PACK (50 pcs./pkg.)



Part Number		Extrusion (Series)	Unit Price 1 ~ 2 pkg(s).	Volume Discount Rate 3~30
Type	No.			
HFCC	5PACK	HFS5		
	6PACK	HFS6		
	8PACK	HFS8 HFS8-45		

When using No. 8 for HFS8-45, the fit becomes slightly firmer.
50 pcs. per pkg.



Alterations

Part Number - (SET)
HFCC6PACK - SET


Alteration	Code
Set of 300 pcs.	SET

When ordering, please note the quantity. 300 pcs. will be delivered for an order of one HFCC5PACK-SET.

Ordering Example
Part Number
HFCC6PACK




Band




Mounting

Turns 90 deg.



Cables can be fixed to extrusions with cable ties.


Band Binding Range



Bands are not included.


Cable Covers

Cable Covers



RoHS10

HSCE (Standard Length) HSCEF (Configurable Length)



Material: Polypropylene Resin

Cable Covers Standard Length


Part Number		Color	L m	Applicable Extrusion (Series)	Unit Price 1 ~ 5 pc(s).	Volume Discount Rate 6~20
Type	No.					
HSCE	8	S (Light Gray)	2	HFS8		

Cable Covers Configurable Length

Part Number		Color	L 1mm Increment	Applicable Extrusion (Series)	Unit Price/m 1 ~ 20 pc(s).
Type	No.				
HSCEF	8	S (Light Gray)	100~2000	HFS8	


Unit Price/m x Specified Full Length = Price

Cable Cover L-Shaped Connectors




RoHS10


HSCELA (Vertical L-shaped)




When these parts are set up



HSCELB (Flat L-shaped)



When these parts are set up




Arrow View A

Material: ABS Resin

Part Number		Color	Unit Price 1 ~ 5 pc(s).	Volume Discount Rate 6~20
Type	No.			
HSCELA HSCELB	8	S (Light Gray)		




Example



Example

Part Number - Color - L
HSCE8 - S - 2
HSCELB8 - S



Encase a cable duct along an aluminum extrusion with 2 pcs. of L-shaped connectors.