SCHAEFFLER



LR40X45X20,5

Inner ring

Schaeffler ID:
0000598110000

Inner ring LR, cylindrical

Technical information



Main Dimensions & Performance Data

d	40 mm	Bore diameter
F	45 mm	Raceway diameter inner ring
B	20,5 mm	Width
r_{min}	0,3 mm	Minimum chamfer dimension
	30 °	Chamfer angle
	52,7 g	Weight

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all further information and guidelines for this product. For further information you can use the contact form on our website.