

AP SAKB/C/T KRG**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



AP 014672



End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

General ordering data

| | |
|------------|--|
| Version | SAK Series, End plate, 3 mm, dark beige, yellow, Direct mounting |
| Order No. | 0146720000 |
| Type | AP SAKB/C/T KRG |
| GTIN (EAN) | 4008 190027995 |
| Qty. | 20 pc(s). |

Creation date March 1, 2023 2:22:35 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

AP SAKB/C/T KRG

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Depth | 36.5 mm | Depth (inches) | 1.437 inch |
| Height | 65 mm | Height (inches) | 2.559 inch |
| Width | 3 mm | Width (inches) | 0.118 inch |
| Net weight | 9.24 g | | |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|--------|
| Storage temperature | -25 °C...55 °C | Continuous operating temp., min. | -60 °C |
| Continuous operating temp., max. | 130 °C | | |

Material data

| | | | |
|---------------------------|-----|--------|--------------------|
| Material | KrG | Colour | dark beige, yellow |
| UL 94 flammability rating | V-0 | | |

System specifications

| | |
|---------|-----------|
| Version | End plate |
|---------|-----------|

Additional technical data

| | | | |
|---------------------|-----------------|---------|-----|
| Installation advice | Direct mounting | Snap-on | Yes |
|---------------------|-----------------|---------|-----|

Dimensions

| | |
|--------------|-------|
| TS 35 offset | 22 mm |
|--------------|-------|

General

| | |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000886 | ETIM 7.0 | EC000886 |
| ETIM 8.0 | EC000886 | ECLASS 9.1 | 27-14-11-33 |
| ECLASS 10.0 | 27-14-11-33 | ECLASS 11.0 | 27-14-11-33 |
| ECLASS 12.0 | 27-14-11-33 | | |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Catalogues | Catalogues in PDF-format |