

**QL 2 SAK2.5****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Product image**

Similar to illustration

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

Version	SAK Series, Cross-connector, for cross-connection link, Number of poles: 2
Order No.	<a href="#">0155900000</a>
Type	QL 2 SAK2.5
GTIN (EAN)	4008190145408
Qty.	100 pc(s).

**QL 2 SAK2.5**

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	0.6 mm	Depth (inches)	0.024 inch
Height	6 mm	Height (inches)	0.236 inch
Width	11 mm	Width (inches)	0.433 inch
Net weight	0.255 g		

**Temperatures**

Storage temperature -25 °C...55 °C

**Material data**

Material Copper Colour grey

**System specifications**

Version for cross-connection link

**Additional technical data**Explosion-tested version No Installation advice Direct mounting  
Type of fixing when screwed in**Cross-connector**Number of cross-connected terminals 2 Rated current, 2-pole 41 A  
Rated current, multi-pole 41 A Type Cross-connector**Dimensions**

Pitch in mm (P) 6 mm

**General**

Installation advice Direct mounting Number of poles 2

**Rating data**

Rated current 32 A

**Classifications**

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40

**Approvals**

ROHS Conform

**Data sheet**

**QL 2 SAK2.5**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

**Downloads**

Engineering Data	<a href="#">WSCAD</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>