

**QL 2 SAKG40/35****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Similar to illustration

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

Version	SAK Series, Cross-connector, Cross-connector, Number of poles: 2
Order No.	<a href="#">0211400000</a>
Type	QL 2 SAKG40/35
GTIN (EAN)	4008 19000494 1
Qty.	5 pc(s).

Creation date February 28, 2023 4:52:39 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

## QL 2 SAKG40/35

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Depth	5 mm	Depth (inches)	0.197 inch
Height	25 mm	Height (inches)	0.984 inch
Width	71 mm	Width (inches)	2.795 inch
Net weight	66.8 g		

### Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

### Material data

Material	CuSn	Colour	grey
----------	------	--------	------

### System specifications

Version	Cross-connector
---------	-----------------

### Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in	Type of mounting	when screwed in

### Cross-connector

Number of cross-connected terminals	2	Rated current, 2-pole	232 A
Rated current, multi-pole	232 A	Type	Cross-connector

### Dimensions

Pitch in mm (P)	40 mm
-----------------	-------

### General

Installation advice	Direct mounting	Number of poles	2
---------------------	-----------------	-----------------	---

### Rating data

Rated current	232 A
---------------	-------

### Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	86596b21-b817-43a9-8e4c-ac00e41b9a24

### Approvals

ROHS	Conform
------	---------

Creation date February 28, 2023 4:52:39 PM CET

**Data sheet**

**QL 2 SAKG40/35**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

**Downloads**

---

User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

---